


### Glass-Filled UHMW Polyethylene Plastic

Glass filler makes this material stronger and more abrasion resistant than standard UHMW.



Part Number	Shape	Material	Grade	Thickness	Width	Length	Color	Clarity	Backing Type	Specs Met
PS-UHMW-GF-49	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-77	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-105	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-133	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-50	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-78	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-106	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-134	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-51	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-79	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-107	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-135	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-52	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1/2"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-80	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1/2"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-108	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1/2"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-136	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1/2"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-57	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-85	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-113	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-141	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-165	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-185	Bar	UHMW Polyethylene	Glass-Filled	1"	1"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-58	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-86	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-114	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-142	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-166	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-186	Bar	UHMW Polyethylene	Glass-Filled	1"	1"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-59	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-87	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-115	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-143	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-167	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-187	Bar	UHMW Polyethylene	Glass-Filled	1"	1"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-60	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-88	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-116	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-144	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-168	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-188	Bar	UHMW Polyethylene	Glass-Filled	1"	1"	48"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-61	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-89	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-117	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-145	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-169	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-189	Bar	UHMW Polyethylene	Glass-Filled	1"	1-1/2"	12"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-62	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-90	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-118	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-146	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-170	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-190	Bar	UHMW Polyethylene	Glass-Filled	1"	1-1/2"	24"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-63	Bar	UHMW Polyethylene	Glass-Filled	3/16"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-91	Bar	UHMW Polyethylene	Glass-Filled	1/4"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-119	Bar	UHMW Polyethylene	Glass-Filled	3/8"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-147	Bar	UHMW Polyethylene	Glass-Filled	1/2"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-171	Bar	UHMW Polyethylene	Glass-Filled	3/4"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB
PS-UHMW-GF-191	Bar	UHMW Polyethylene	Glass-Filled	1"	1-1/2"	36"	Blue	Opaque	Plain	UL 94 HB