

Plastic Angles

Polycarbonate Plastic

Polycarbonate is clear for applications that require seeing through the plastic and has excellent resistance to impact, shock, and strikes.



Part Number	Shape	Material	Grade	Wall Thickness	Outside Height	Outside Width	Inside Height	Inside Width	Length	Color	Clarity	Specs Met
BULK-PA-PC-1	90 Degree Angle	Polycarbonate	Standard	0.05"	1/2"	1/2"	0.45"	0.45"	6 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-2	90 Degree Angle	Polycarbonate	Standard	0.05"	1"	1"	0.95"	0.95"	6 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-3	90 Degree Angle	Polycarbonate	Standard	0.05"	1-1/2"	1-1/2"	1.45"	1.45"	6 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-10	90 Degree Angle	Polycarbonate	Standard	0.05"	1/2"	1/2"	0.45"	0.45"	3 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-11	90 Degree Angle	Polycarbonate	Standard	0.05"	1"	1"	0.95"	0.95"	3 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-12	90 Degree Angle	Polycarbonate	Standard	0.05"	1-1/2"	1-1/2"	1.45"	1.45"	3 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-7	90 Degree Angle	Polycarbonate	Standard	0.05"	1/2"	1/2"	0.45"	0.45"	2 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-8	90 Degree Angle	Polycarbonate	Standard	0.05"	1"	1"	0.95"	0.95"	2 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-9	90 Degree Angle	Polycarbonate	Standard	0.05"	1-1/2"	1-1/2"	1.45"	1.45"	2 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-4	90 Degree Angle	Polycarbonate	Standard	0.05"	1/2"	1/2"	0.45"	0.45"	1 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-5	90 Degree Angle	Polycarbonate	Standard	0.05"	1"	1"	0.95"	0.95"	1 ft.	Clear	Clear	UL 94 V-2
BULK-PA-PC-6	90 Degree Angle	Polycarbonate	Standard	0.05"	1-1/2"	1-1/2"	1.45"	1.45"	1 ft.	Clear	Clear	UL 94 V-2