

# Clean Regulator/Fluoro-resin Type

# SRF Series

RoHS

## How to Order

### Integrated fittings



SRF **1** **0** - **S** **07** [ ] - [ ]

Body size  

1
3
5

Integrated fittings (LQ2)

Made to Order  
 (Refer to page 887 for details.)

Nil	Standard
X401	Rotating the mounting hole 90°

Pilot port thread type

Nil	Rc 1/8
N	NPT 1/8

Applicable tubing size (O.D. x I.D.)

Metric size

Symbol	Applicable tubing size	Applicable model		
		SRF10	SRF30	SRF50
04	4 x 3	●		
06	6 x 4	○	●	
08	8 x 6		●	
10	10 x 8			○
12	12 x 10			●
19	19 x 16			○

○: Basic size ●: With reducer

Inch size

Symbol	Applicable tubing size	Applicable model		
		SRF10	SRF30	SRF50
03	1/8" x 0.086"	●		
05	3/16" x 1/8"	●		
07	1/4" x 5/32"	○	●	
11	3/8" x 1/4"			○
13	1/2" x 3/8"			●
19	3/4" x 5/8"			○

○: Basic size ●: With reducer

Note) Tubing size is interchangeable by replacing the reducer insert bushing nut.  
 For details, refer to Best Pneumatics No. 9.

### With nut



SRF **1** **0** **S** - **1** **S** **07** **11** [ ] - [ ]

Body size  

1
3
5

Fitting type

Symbol	Applicable fittings
1	LQ1
2	LQ2

Pilot port thread type

Nil	Rc 1/8
N	NPT 1/8

Made to Order  
 (Refer to page 887 for details.)

Nil	Standard
X401	Rotating the mounting hole 90°

Fitting size (IN side)

Symbol	Fitting size <sup>Note 2)</sup>	Fitting type	Applicable model		
			SRF10	SRF30	SRF50
07	2		○		
11	3		●		
13	4	LQ1, 2		○	
19	5				○
25 <sup>Note 1)</sup>	6	LQ1			●

○: Basic size ●: With plug-in reducer

Fitting size (OUT side)

Symbol	Applicable fitting size <sup>Note 2)</sup>	Fitting type	Applicable model		
			SRF10	SRF30	SRF50
Nil	Same as IN side	—	—	—	—
07	2		○		
11	3		●		
13	4	LQ1, 2		○	
19	5				○
25 <sup>Note 1)</sup>	6	LQ1			●

○: Basic size ●: With reducer

Note 1) Fitting type: LQ1 only

Note 2) Refer to How to Order (LQ□□-S) on page 879 for applicable fittings without nut (LQ type).

Select fittings of the same type and size as the one fitted to the regulator side.

### Tube extensions



SRF **1** **0** - **T** **07** [ ] - [ ]

Body size  

1
3
5

Tubing size (O.D.)

Symbol	Tubing size	Applicable model
07	1/4"	SRF10
11	3/8"	SRF30
19	3/4"	SRF50

Made to Order  
 (Refer to page 887 or details.)

Nil	Standard
X401	Rotating the mounting hole 90°

Pilot port thread type

Nil	Rc 1/8
N	NPT 1/8