

Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

Double Ended Hammer



- Features**
- The head is completely quenched (hardness 50 to 55 degrees), the handle is lighter than the oak, strong and elastic hickory is used.
- Materials**
- Head: Carbon steel
 - Handle: Hickory
- Origin**
- China

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Head Diameter (mm)	Head Length (mm)	Total Length (mm)	SPQ (piece)	Weight (kg)
232-2439	TRH-20	¥1,889	¥2,040	2 Pound	38	105.4	355	4	0.9
232-2447	TRH-30	¥2,129	¥2,300	3 Pound	43	118.0	361	4	1.3
232-2455	TRH-40	¥2,667	¥2,880	4 Pound	47	130.0	400	4	1.8

Handle Accessories •Wedge: 1 Piece

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Hammer Designation		Compatible Model	SPQ (piece)	Weight (g)
				(pound)	(g)			
288-9684	TRH-20K	¥778	¥840	#2	900	TRH-20	12	220
288-9706	TRH-30K	¥778	¥840	#3	1300	TRH-30	12	220
293-4914	TRH-40K	¥778	¥840	#4	1800	TRH-40	12	220

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Double Ended Hammer



- Features**
- Excellent in durability and safety with adoption of fiberglass handle.
 - Adopts a soft grip which is hard to slip and is gentle to the hands.
 - The head is completely quenched.
- Materials**
- Head: Carbon steel (quenching hardness HRC45 to 60)
 - Handle: Polypropylene (PP), thermoplastic rubber (TPR)
 - Handle core: Fiberglass
- Origin**
- China

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION


SPQ: 4 Pieces

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Head Diameter (mm)	Head Length (mm)	Total Length (mm)	Weight (kg)
415-8717	TRH-25G	¥2,546	¥2,750	2 1/2 Pound	40.5	121	361	1.43
415-8725	TRH-30G	¥2,768	¥2,990	3 Pound	43.0	128	400	1.68
415-8733	TRH-40G	¥3,675	¥3,970	4 Pound	47.0	140	400	2.10

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Double Ended Hammer



- Features**
- Excellent in durability and safety with adoption of fiberglass handle.
 - Connection between the head and the handle is protected by an attached protect ring.
- Materials**
- Head: Carbon steel
 - Handle core: Fiberglass
- Origin**
- Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

SPQ: 2 Pieces

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Head Diameter (mm)	Head Length (mm)	Total Length (mm)	Weight (kg)
366-9297	TRH-60	¥5,601	¥6,050	6 Pound	54	161	892	3.38
366-9301	TRH-80	¥6,619	¥7,150	8 Pound	59	176	897	4.74
366-9246	TRH-100	¥7,637	¥8,250	10 Pound	64	188	902	5.75
366-9254	TRH-120	¥8,961	¥9,680	12 Pound	67	201	905	6.20
366-9262	TRH-140	¥9,979	¥10,780	14 Pound	70	212	908	7.53
366-9271	TRH-160	¥10,998	¥11,880	16 Pound	73	224	911	8.00
366-9289	TRH-200	¥13,035	¥14,080	20 Pound	78	242	918	9.80

Contact us:0120-509-849 <http://www.orange-book.com/>

OHSO **Stock 91 Items**

Scaffolding Hammer



- Features**
- Can be used for assembling and dismantling wedge scaffold.
 - A safety cord can be attached to the end of the handle to prevent it from being dropped.
- Materials**
- Head: Carbon steel
 - Handle: Quenched pipe
 - Grip: Polyvinyl chloride (PVC)
- Origin**
- Japan

Order Unit: 1 Piece

SUSA MANUFACTURING.CO.LTD

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Designation	Head Diameter (mm)	Head Length (mm)	Total Length (mm)	SPQ (piece)	Weight (kg)
818-4288	033829	¥2,841	¥3,070	Lightweight	33 x 36	80	280	6	0.80
818-4289	033805	¥3,110	¥3,360	Medium-weight	33 x 35	80	280	6	0.90
818-4290	033850	¥3,230	¥3,490	Heavy-weight	33 x 35	100	280	6	1.10
818-4291	033812	¥3,619	¥3,910	Silent	Steel part 38/Resin part 38	80	280	6	0.85

Replacement Head for silent type Materials •lonomer resin

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Head Diameter (mm)	Compatible Model	SPQ (piece)	Weight (g)
818-4292	033836	¥1,286	¥1,390	38	033812	6	20

Contact us:0256-46-4834 <http://www.tonkachi.com/>

Single-Ended Hammers

Double-Ended Hammers

Combination Hammers

Shock-Less Hammers

Resin Hammers • Rubber Hammers

Nonferrous Hammers

Stainless Steel Hammers

Wood Hammers

Stone Hammers

Welding Hammers

Sheet Metal Hammers

Claw Hammers

Centering Hammers

Hammers for Woodwork

Hammers for Electric Work

Test Hammers

Wedges

Grip Tapes

Bars

Chisels

Stamps

Date Marks

Industrial Stamps

Punches