

Prices displayed include 8% tax.


TRUSCO
Stock 38,650 Items

"Adjustable Wrench with Grip"



- Features
- Elastomer resin grip so it fits your hand, making it less slippery.
 - The grip end can also be used as a box end wrench.
- Origin
- China

Item No. Suffix	Color
-R	Red
-GN	Green



Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	Opposite Side Dimension (mm)	SPQ (piece)	Weight (g)
299-4496	TRMG-150-R	¥1,500	¥1,620	160	24	10	5	145
299-4500	TRMG-200-R	¥1,722	¥1,860	210	30	13	5	280
299-4518	TRMG-250-R	¥2,193	¥2,370	260	35	17	5	430
299-4526	TRMG-300-R	¥2,823	¥3,050	310	41	17	5	780
299-4534	TRMG-150-GN	¥1,500	¥1,620	160	24	10	5	145
299-4542	TRMG-200-GN	¥1,722	¥1,860	210	30	13	5	280
299-4551	TRMG-250-GN	¥2,193	¥2,370	260	35	17	5	430
299-4569	TRMG-300-GN	¥2,823	¥3,050	310	41	17	5	780

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO
Stock 38,650 Items

"Adjustable Wrench with Grip"

RoHS



- Features
- With the elastomer resin grip, it fits hands, making it less slippery.
 - Lightweight, wide type
 - With a scale.
- Origin
- Taiwan



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
488-8561	TMWN-100	¥1,490	¥1,610	108	17.0	50	60
488-8570	TMWN-150	¥1,602	¥1,730	157	23.9	10	110
488-8588	TMWN-200	¥1,740	¥1,880	206	28.6	5	230
488-8596	TMWN-250	¥2,240	¥2,420	254	32.8	5	400
488-8600	TMWN-300	¥2,934	¥3,170	304	38.0	5	600
488-8618	TMWN-375	¥5,073	¥5,480	381	50.0	5	1200

Contact us:0120-509-849 <http://www.orange-book.com/>

LOBTEX
Stock 1,809 Items

Adjustable Angle Wrench (with insulated grip)

- Features
- Grip with the insulation function.
 - Wide opening that opens up to 36mm.
 - Test voltage is 20kV/minute. (working temperature range: -20 to 70° C)
- Origin
- Japan



Warning

- The insulation function is applied only to the molded cover (grip) part.

Order Unit: 1 Piece

(Price revision date: Jan, 2016) LOBTEX Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
342-6343	S36	¥4,941	¥5,230	260	36	6	500

Contact us:072-980-1111 <http://www.lobtex.co.jp/>

ENGINEER
Stock 641 Items

Adjustable Wrench

RoHS

- Features
- A soft grip that fits your hand.
- Origin
- Japan



Order Unit: 1 Piece

(Price revision date: Jul, 2015) ENGINEER INC.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Max Opening (mm)	SPQ (piece)	Weight (g)
368-8895	TWM-04	¥2,538	¥2,530	100	13	5	64
368-8879	TWM-01	¥2,366	¥2,360	155	20	5	137
368-8887	TWM-02	¥2,588	¥2,580	210	25	5	257
395-5664	TWM-05	¥2,739	¥2,730	260	30	5	410

Contact us:06-6974-0100 <http://www.engineer.jp/>