








Type	Gate			Globe			Swing Check			Lift Check			Strainer			
<b>VA-Series</b>																
Fig	<b>10-USRF-VA</b>			<b>10-UGF-VA</b>			<b>10-UNSF-VA</b>			<b>10-UNF-VA</b>			<b>10-UTF-VA</b>			
Product Code	<b>803J</b>						<b>805J</b>									
inch	mm	L	H	D	L	H	D	L	H	D	L	H		L	H	H1*
1/2	15	108	201	90							108	74				
3/4	20	117	211	90							117	76				
1	25	127	224	100							127	76				
1	32	140	240	100							140	84				
1 1/2	40	165	284	140							165	86				
2	50	178	336	160	203	234	160	203	121							
2 1/2	65	190	374	180	216	247	180	216	134					270	154	214
3	80	203	444	200	241	292	200	241	148					290	189	263
4	100	229	523	225	292	324	225	292	162					350	227	320
5	125	254	606	250				330	192					390	268	383
6	150	267	711	250				356	217					440	316	451
8	200	292	924	300				495	264					540	384	554
10	250	330	1126	350										760	536	753
Body	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Bonnet/Cap/Cover	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Stem	Stainless Steel			Stainless Steel												
Disc/Ball	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel						
Hinge Pin							Stainless Steel									
Plug							Stainless Steel									
Screen													Stainless Steel			
Arm							Stainless Steel									
Note													*Height for removing the screen			

Type	Gate			Gate			Globe			Globe			Swing Check			
<b>U-Series</b>																
Fig	<b>US-N</b>			<b>USF-N</b>			<b>UG-N</b>			<b>UGF-N</b>			<b>UNS-N</b>			
Product Code	<b>802</b>			<b>802J</b>			<b>800</b>			<b>800J</b>			<b>804</b>			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	
1/4	8							44	68	55						
3/8	10							48	68	55						
1/2	15	54	97	70	85	100	70	52	68	55	85	112	70	65	45	
3/4	20	58	102	70	95	106	70	60	94	70	95	113	70	80	55	
1	25	65	112	80	100	116	80	72	101	70	110	143	100	90	61	
1 1/4	32	74	123	80	110	128	80	80	124	90	130	152	100	105	71	
1 1/2	40	78	150	100	125	170	100	90	138	90	150	172	110	120	72	
2	50	87	167	100	140	188	100	100	153	100	180	190	125	140	81	
Body	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Bonnet/Cap/Cover				Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Stem	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel						
Disc/Ball	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Packing	Flexible Graphite+PTFE Braided Packing			Flexible Graphite+PTFE Braided Packing			Flexible Graphite+PTFE Braided Packing			Flexible Graphite+PTFE Braided Packing						
Hinge Pin													Stainless Steel			
Plug													Stainless Steel			
Note																