


Semi-Closed Cell EPDM

EPDM is the most weather resistant foam, with a wide range of chemical compatibility, steam resistance, and good temperature range. Also known as crushed-cell foam, semi-closed foam is highly conformable like an open-cell foam but forms a tight seal and prevents air, water, and fluids from passing through it like a closed-cell foam.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture
ZUSA-CESR-64	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-73	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-86	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-103	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-65	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-74	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-87	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-104	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-66	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-75	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-88	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-105	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-67	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-76	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-89	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-106	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-77	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-90	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-107	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-78	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-91	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-108	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-92	Strip	Semi-Closed Cell	EPDM	Standard	3/4"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-109	Strip	Semi-Closed Cell	EPDM	Standard	3/4"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-93	Strip	Semi-Closed Cell	EPDM	Standard	1"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-110	Strip	Semi-Closed Cell	EPDM	Standard	1"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CESR-193	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-202	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-215	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-232	Strip	Semi-Closed Cell	EPDM	Standard	1/16"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-194	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-203	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-216	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-233	Strip	Semi-Closed Cell	EPDM	Standard	1/8"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-195	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-204	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-217	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-234	Strip	Semi-Closed Cell	EPDM	Standard	3/16"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-196	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-205	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-218	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-235	Strip	Semi-Closed Cell	EPDM	Standard	1/4"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-206	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-219	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-236	Strip	Semi-Closed Cell	EPDM	Standard	3/8"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-207	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-220	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-237	Strip	Semi-Closed Cell	EPDM	Standard	1/2"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-221	Strip	Semi-Closed Cell	EPDM	Standard	3/4"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-238	Strip	Semi-Closed Cell	EPDM	Standard	3/4"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-222	Strip	Semi-Closed Cell	EPDM	Standard	1"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-239	Strip	Semi-Closed Cell	EPDM	Standard	1"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CESR-28	Sheet	Semi-Closed Cell	EPDM	Standard	1/16"	12"	12"	Black	Extra Soft	Plain	Textured
ZUSA-CESR-37	Sheet	Semi-Closed Cell	EPDM	Standard	1/16"	12"	24"	Black	Extra Soft	Plain	Textured
ZUSA-CESR-55	Sheet	Semi-Closed Cell	EPDM	Standard	1/16"	36"	36"	Black	Extra Soft	Plain	Textured
ZUSA-CESR-29	Sheet	Semi-Closed Cell	EPDM	Standard	1/8"	12"	12"	Black	Extra Soft	Plain	Textured