


Super Cushioning Polyurethane Foam

Polyurethane Foam

Polyurethane foam is a versatile material used for shock absorption and cushioning. It is a common choice for packaging and insulation applications.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture
ZUSA-PU-49	Strip	Open Cell	Polyurethane	Standard	1/8"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-55	Strip	Open Cell	Polyurethane	Standard	1/8"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-67	Strip	Open Cell	Polyurethane	Standard	1/8"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-50	Strip	Open Cell	Polyurethane	Standard	1/4"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-56	Strip	Open Cell	Polyurethane	Standard	1/4"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-68	Strip	Open Cell	Polyurethane	Standard	1/4"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-51	Strip	Open Cell	Polyurethane	Standard	1/2"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-57	Strip	Open Cell	Polyurethane	Standard	1/2"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-69	Strip	Open Cell	Polyurethane	Standard	1/2"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-58	Strip	Open Cell	Polyurethane	Standard	1"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-70	Strip	Open Cell	Polyurethane	Standard	1"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-71	Strip	Open Cell	Polyurethane	Standard	2"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-73	Strip	Open Cell	Polyurethane	Standard	1/8"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-79	Strip	Open Cell	Polyurethane	Standard	1/8"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-91	Strip	Open Cell	Polyurethane	Standard	1/8"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-74	Strip	Open Cell	Polyurethane	Standard	1/4"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-80	Strip	Open Cell	Polyurethane	Standard	1/4"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-92	Strip	Open Cell	Polyurethane	Standard	1/4"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-75	Strip	Open Cell	Polyurethane	Standard	1/2"	1/2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-81	Strip	Open Cell	Polyurethane	Standard	1/2"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-93	Strip	Open Cell	Polyurethane	Standard	1/2"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-82	Strip	Open Cell	Polyurethane	Standard	1"	1"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-94	Strip	Open Cell	Polyurethane	Standard	1"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-95	Strip	Open Cell	Polyurethane	Standard	2"	2"	6 ft.	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-19	Sheet	Open Cell	Polyurethane	Standard	1/8"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-13	Sheet	Open Cell	Polyurethane	Standard	1/8"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-7	Sheet	Open Cell	Polyurethane	Standard	1/8"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-1	Sheet	Open Cell	Polyurethane	Standard	1/8"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-20	Sheet	Open Cell	Polyurethane	Standard	1/4"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-14	Sheet	Open Cell	Polyurethane	Standard	1/4"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-8	Sheet	Open Cell	Polyurethane	Standard	1/4"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-2	Sheet	Open Cell	Polyurethane	Standard	1/4"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-21	Sheet	Open Cell	Polyurethane	Standard	1/2"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-15	Sheet	Open Cell	Polyurethane	Standard	1/2"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-9	Sheet	Open Cell	Polyurethane	Standard	1/2"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-3	Sheet	Open Cell	Polyurethane	Standard	1/2"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-22	Sheet	Open Cell	Polyurethane	Standard	1"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-16	Sheet	Open Cell	Polyurethane	Standard	1"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-10	Sheet	Open Cell	Polyurethane	Standard	1"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-4	Sheet	Open Cell	Polyurethane	Standard	1"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-23	Sheet	Open Cell	Polyurethane	Standard	2"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-17	Sheet	Open Cell	Polyurethane	Standard	2"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-11	Sheet	Open Cell	Polyurethane	Standard	2"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-5	Sheet	Open Cell	Polyurethane	Standard	2"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-24	Sheet	Open Cell	Polyurethane	Standard	4"	13"	13"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-18	Sheet	Open Cell	Polyurethane	Standard	4"	19"	19"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-12	Sheet	Open Cell	Polyurethane	Standard	4"	39"	39"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-6	Sheet	Open Cell	Polyurethane	Standard	4"	39"	78"	Black	Extra Soft (0 - 4 psi)	Plain	Smooth
ZUSA-PU-43	Sheet	Open Cell	Polyurethane	Standard	1/8"	13"	13"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-37	Sheet	Open Cell	Polyurethane	Standard	1/8"	19"	19"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-31	Sheet	Open Cell	Polyurethane	Standard	1/8"	39"	39"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-25	Sheet	Open Cell	Polyurethane	Standard	1/8"	39"	78"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-44	Sheet	Open Cell	Polyurethane	Standard	1/4"	13"	13"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-38	Sheet	Open Cell	Polyurethane	Standard	1/4"	19"	19"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-32	Sheet	Open Cell	Polyurethane	Standard	1/4"	39"	39"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth
ZUSA-PU-26	Sheet	Open Cell	Polyurethane	Standard	1/4"	39"	78"	Black	Extra Soft (0 - 4 psi)	Acrylic Adhesive	Smooth