


High Strength Buna-N Rubber

This formulation is stronger and more durable than standard Buna-N for more demanding applications. Buna-N is ideal for oils, greases, fuels, and petroleum applications. It also works well with water and mild chemicals and has excellent physical properties making it tough and durable.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-BHS40-862	Strip	Buna-N	High Strength	40A	1/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-863	Strip	Buna-N	High Strength	40A	1/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-864	Strip	Buna-N	High Strength	40A	1/32"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-871	Strip	Buna-N	High Strength	40A	1/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-872	Strip	Buna-N	High Strength	40A	1/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-880	Strip	Buna-N	High Strength	40A	3/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-881	Strip	Buna-N	High Strength	40A	3/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-882	Strip	Buna-N	High Strength	40A	3/32"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-888	Strip	Buna-N	High Strength	40A	1/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-889	Strip	Buna-N	High Strength	40A	1/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-890	Strip	Buna-N	High Strength	40A	1/8"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-899	Strip	Buna-N	High Strength	40A	3/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-900	Strip	Buna-N	High Strength	40A	3/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-905	Strip	Buna-N	High Strength	40A	1/4"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-906	Strip	Buna-N	High Strength	40A	1/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-907	Strip	Buna-N	High Strength	40A	1/4"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-914	Strip	Buna-N	High Strength	40A	3/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-915	Strip	Buna-N	High Strength	40A	3/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-916	Strip	Buna-N	High Strength	40A	3/8"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-920	Strip	Buna-N	High Strength	40A	1/2"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-921	Strip	Buna-N	High Strength	40A	1/2"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-927	Strip	Buna-N	High Strength	40A	3/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-928	Strip	Buna-N	High Strength	40A	1"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-867	Strip	Buna-N	High Strength	40A	1/32"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-868	Strip	Buna-N	High Strength	40A	1/32"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-869	Strip	Buna-N	High Strength	40A	1/32"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-878	Strip	Buna-N	High Strength	40A	1/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-886	Strip	Buna-N	High Strength	40A	3/32"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-896	Strip	Buna-N	High Strength	40A	1/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-897	Strip	Buna-N	High Strength	40A	1/8"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-912	Strip	Buna-N	High Strength	40A	1/4"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-918	Strip	Buna-N	High Strength	40A	3/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-925	Strip	Buna-N	High Strength	40A	1/2"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-929	Strip	Buna-N	High Strength	40A	1"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS40-930	Strip	Buna-N	High Strength	40A	1"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 410
BULK-RS-BHS50-77	Strip	Buna-N	High Strength	50A	1/32"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-78	Strip	Buna-N	High Strength	50A	1/32"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-79	Strip	Buna-N	High Strength	50A	1/32"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-80	Strip	Buna-N	High Strength	50A	1/32"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-850	Strip	Buna-N	High Strength	50A	1/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-84	Strip	Buna-N	High Strength	50A	1/32"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-851	Strip	Buna-N	High Strength	50A	1/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-413	Strip	Buna-N	High Strength	50A	1/32"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-419	Strip	Buna-N	High Strength	50A	1/32"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-57	Strip	Buna-N	High Strength	50A	1/16"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-58	Strip	Buna-N	High Strength	50A	1/16"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-59	Strip	Buna-N	High Strength	50A	1/16"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-60	Strip	Buna-N	High Strength	50A	1/16"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-859	Strip	Buna-N	High Strength	50A	1/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-64	Strip	Buna-N	High Strength	50A	1/16"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-860	Strip	Buna-N	High Strength	50A	1/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-414	Strip	Buna-N	High Strength	50A	1/16"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-861	Strip	Buna-N	High Strength	50A	1/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-420	Strip	Buna-N	High Strength	50A	1/16"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-400	Strip	Buna-N	High Strength	50A	3/32"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-402	Strip	Buna-N	High Strength	50A	3/32"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-403	Strip	Buna-N	High Strength	50A	3/32"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510
BULK-RS-BHS50-404	Strip	Buna-N	High Strength	50A	3/32"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 510