

**Metal Detectable FDA Silicone Rubber**

This formulation contains metal fillers which allow the silicone rubber to be picked up by metal detection systems should they tear or fall into the process stream. It is also made of FDA compliant materials for food, beverage, and pharmaceutical applications. Silicone has excellent weathering properties and can withstand high temperatures.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-S60MD-1	Roll	Silicone	Metal Detectable	60A	1/32"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-2	Roll	Silicone	Metal Detectable	60A	1/16"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-3	Roll	Silicone	Metal Detectable	60A	1/8"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-4	Roll	Silicone	Metal Detectable	60A	3/16"	36"	50 ft.	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-5	Roll	Silicone	Metal Detectable	60A	1/4"	36"	50 ft.	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-6	Sheet	Silicone	Metal Detectable	60A	1/32"	6"	6"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-7	Sheet	Silicone	Metal Detectable	60A	1/16"	6"	6"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-8	Sheet	Silicone	Metal Detectable	60A	1/8"	6"	6"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-9	Sheet	Silicone	Metal Detectable	60A	3/16"	6"	6"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-10	Sheet	Silicone	Metal Detectable	60A	1/4"	6"	6"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-11	Sheet	Silicone	Metal Detectable	60A	1/32"	12"	12"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-12	Sheet	Silicone	Metal Detectable	60A	1/16"	12"	12"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-13	Sheet	Silicone	Metal Detectable	60A	1/8"	12"	12"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-14	Sheet	Silicone	Metal Detectable	60A	3/16"	12"	12"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-15	Sheet	Silicone	Metal Detectable	60A	1/4"	12"	12"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-16	Sheet	Silicone	Metal Detectable	60A	1/32"	24"	24"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-17	Sheet	Silicone	Metal Detectable	60A	1/16"	24"	24"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-18	Sheet	Silicone	Metal Detectable	60A	1/8"	24"	24"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-19	Sheet	Silicone	Metal Detectable	60A	3/16"	24"	24"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-20	Sheet	Silicone	Metal Detectable	60A	1/4"	24"	24"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-21	Sheet	Silicone	Metal Detectable	60A	1/32"	36"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-22	Sheet	Silicone	Metal Detectable	60A	1/16"	36"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-23	Sheet	Silicone	Metal Detectable	60A	1/8"	36"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-24	Sheet	Silicone	Metal Detectable	60A	3/16"	36"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-25	Sheet	Silicone	Metal Detectable	60A	1/4"	36"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-26	Sheet	Silicone	Metal Detectable	60A	1/32"	6"	6"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-27	Sheet	Silicone	Metal Detectable	60A	1/16"	6"	6"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-28	Sheet	Silicone	Metal Detectable	60A	1/8"	6"	6"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-29	Sheet	Silicone	Metal Detectable	60A	3/16"	6"	6"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-30	Sheet	Silicone	Metal Detectable	60A	1/4"	6"	6"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-31	Sheet	Silicone	Metal Detectable	60A	1/32"	12"	12"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-32	Sheet	Silicone	Metal Detectable	60A	1/16"	12"	12"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-33	Sheet	Silicone	Metal Detectable	60A	1/8"	12"	12"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-34	Sheet	Silicone	Metal Detectable	60A	3/16"	12"	12"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-35	Sheet	Silicone	Metal Detectable	60A	1/4"	12"	12"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-36	Sheet	Silicone	Metal Detectable	60A	1/32"	24"	24"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-37	Sheet	Silicone	Metal Detectable	60A	1/16"	24"	24"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-38	Sheet	Silicone	Metal Detectable	60A	1/8"	24"	24"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-39	Sheet	Silicone	Metal Detectable	60A	3/16"	24"	24"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-40	Sheet	Silicone	Metal Detectable	60A	1/4"	24"	24"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-41	Sheet	Silicone	Metal Detectable	60A	1/32"	36"	36"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-42	Sheet	Silicone	Metal Detectable	60A	1/16"	36"	36"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-43	Sheet	Silicone	Metal Detectable	60A	1/8"	36"	36"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-44	Sheet	Silicone	Metal Detectable	60A	3/16"	36"	36"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-45	Sheet	Silicone	Metal Detectable	60A	1/4"	36"	36"	Blue	High Temp Adhesive	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-46	Strip	Silicone	Metal Detectable	60A	1/32"	1/2"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-47	Strip	Silicone	Metal Detectable	60A	1/16"	1/2"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-48	Strip	Silicone	Metal Detectable	60A	1/8"	1/2"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-49	Strip	Silicone	Metal Detectable	60A	3/16"	1/2"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-50	Strip	Silicone	Metal Detectable	60A	1/4"	1/2"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-51	Strip	Silicone	Metal Detectable	60A	1/32"	1"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-52	Strip	Silicone	Metal Detectable	60A	1/16"	1"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-53	Strip	Silicone	Metal Detectable	60A	1/8"	1"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-54	Strip	Silicone	Metal Detectable	60A	3/16"	1"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608
BULK-RS-S60MD-55	Strip	Silicone	Metal Detectable	60A	1/4"	1"	36"	Blue	Plain	Smooth	ASTM D2000 GE 608