

Antistatic UHMW Polyethylene Plastic

Antistatic filler prevents the buildup of static charges and protects sensitive equipment from damage.



Part Number	Shape	Material	Grade	Thickness	Width	Length	Color	Clarity	Backing Type	Specs Met
PS-UHMW-ESD-43	Bar	UHMW Polyethylene	Antistatic	1/8"	1/2"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-75	Bar	UHMW Polyethylene	Antistatic	3/16"	1/2"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-107	Bar	UHMW Polyethylene	Antistatic	1/4"	1/2"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-139	Bar	UHMW Polyethylene	Antistatic	1/2"	1/2"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-44	Bar	UHMW Polyethylene	Antistatic	1/8"	1/2"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-76	Bar	UHMW Polyethylene	Antistatic	3/16"	1/2"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-108	Bar	UHMW Polyethylene	Antistatic	1/4"	1/2"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-140	Bar	UHMW Polyethylene	Antistatic	1/2"	1/2"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-45	Bar	UHMW Polyethylene	Antistatic	1/8"	1/2"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-77	Bar	UHMW Polyethylene	Antistatic	3/16"	1/2"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-109	Bar	UHMW Polyethylene	Antistatic	1/4"	1/2"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-141	Bar	UHMW Polyethylene	Antistatic	1/2"	1/2"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-46	Bar	UHMW Polyethylene	Antistatic	1/8"	1/2"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-78	Bar	UHMW Polyethylene	Antistatic	3/16"	1/2"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-110	Bar	UHMW Polyethylene	Antistatic	1/4"	1/2"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-142	Bar	UHMW Polyethylene	Antistatic	1/2"	1/2"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-47	Bar	UHMW Polyethylene	Antistatic	1/8"	3/4"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-79	Bar	UHMW Polyethylene	Antistatic	3/16"	3/4"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-111	Bar	UHMW Polyethylene	Antistatic	1/4"	3/4"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-143	Bar	UHMW Polyethylene	Antistatic	1/2"	3/4"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-171	Bar	UHMW Polyethylene	Antistatic	3/4"	3/4"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-48	Bar	UHMW Polyethylene	Antistatic	1/8"	3/4"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-80	Bar	UHMW Polyethylene	Antistatic	3/16"	3/4"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-112	Bar	UHMW Polyethylene	Antistatic	1/4"	3/4"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-144	Bar	UHMW Polyethylene	Antistatic	1/2"	3/4"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-172	Bar	UHMW Polyethylene	Antistatic	3/4"	3/4"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-49	Bar	UHMW Polyethylene	Antistatic	1/8"	3/4"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-81	Bar	UHMW Polyethylene	Antistatic	3/16"	3/4"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-113	Bar	UHMW Polyethylene	Antistatic	1/4"	3/4"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-145	Bar	UHMW Polyethylene	Antistatic	1/2"	3/4"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-173	Bar	UHMW Polyethylene	Antistatic	3/4"	3/4"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-50	Bar	UHMW Polyethylene	Antistatic	1/8"	3/4"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-82	Bar	UHMW Polyethylene	Antistatic	3/16"	3/4"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-114	Bar	UHMW Polyethylene	Antistatic	1/4"	3/4"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-146	Bar	UHMW Polyethylene	Antistatic	1/2"	3/4"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-174	Bar	UHMW Polyethylene	Antistatic	3/4"	3/4"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-51	Bar	UHMW Polyethylene	Antistatic	1/8"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-83	Bar	UHMW Polyethylene	Antistatic	3/16"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-115	Bar	UHMW Polyethylene	Antistatic	1/4"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-147	Bar	UHMW Polyethylene	Antistatic	1/2"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-175	Bar	UHMW Polyethylene	Antistatic	3/4"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-199	Bar	UHMW Polyethylene	Antistatic	1"	1"	12"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-52	Bar	UHMW Polyethylene	Antistatic	1/8"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-84	Bar	UHMW Polyethylene	Antistatic	3/16"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-116	Bar	UHMW Polyethylene	Antistatic	1/4"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-148	Bar	UHMW Polyethylene	Antistatic	1/2"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-176	Bar	UHMW Polyethylene	Antistatic	3/4"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-200	Bar	UHMW Polyethylene	Antistatic	1"	1"	24"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-53	Bar	UHMW Polyethylene	Antistatic	1/8"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-85	Bar	UHMW Polyethylene	Antistatic	3/16"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-117	Bar	UHMW Polyethylene	Antistatic	1/4"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-149	Bar	UHMW Polyethylene	Antistatic	1/2"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-177	Bar	UHMW Polyethylene	Antistatic	3/4"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-201	Bar	UHMW Polyethylene	Antistatic	1"	1"	36"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-54	Bar	UHMW Polyethylene	Antistatic	1/8"	1"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-86	Bar	UHMW Polyethylene	Antistatic	3/16"	1"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-118	Bar	UHMW Polyethylene	Antistatic	1/4"	1"	48"	Black	Opaque	Plain	UL 94 HB
PS-UHMW-ESD-150	Bar	UHMW Polyethylene	Antistatic	1/2"	1"	48"	Black	Opaque	Plain	UL 94 HB