


PCI Express-compliant
High speed GPIB (Low Profile)
GPIB-F-LPE, GPIB-FL-LPE



* Specifications, color and design of the products are subject to change without notice.

Model	Name	Bus analyzer function
GPIB-F-LPE	High speed Multi function GPIB	○
GPIB-FL-LPE	High speed GPIB	None

Features

Complies with the IEEE-488.2 standard

As the board complies with the IEEE-488.2 standard, you can control any external device that supports this standard.

Data transfer speed 1.5Mbyte/sec max.

The maximum data transfer speed for communications is 1.5Mbyte/sec.

Supports bus master operation

The bus master data transfer function enables large quantities of data to be transferred between the board and PC without loading the CPU.

Internal 2Kbyte FIFO buffers for send and receive

The board has separate 2Kbyte FIFO buffers for sending and receiving data, allowing both small and large volumes of data to be transferred at high speed. Interface messages also use a FIFO to enable high-speed transmission.

Built-in GPIB bus analyzer function [only GPIB-F-LPE]

The board features a bus analyzer function. This not only allows the signals on the GPIB bus to be analyzed, but also permits signal analysis to be performed while this product is performing GPIB communications.

Built-in SPAS event function

In addition to the functions of the earlier GPIB controller (μPD7210), the board also supports the SPAS event generated when a serial poll occurs. This gives you a high level of flexibility in constructing your system.

Internal high-precision timer

The board includes a high-precision application timer to allow accurate time monitoring to be performed under Windows.

Long term availability

As the board uses a high-speed GPIB controller developed by CONTEC (compatible with the μPD7210 register), reliable long term availability is ensured.

Diagnosis program

A diagnosis program is supplied to support system development. The diagnostic program can be used to check hardware operation (interrupts and I/O addresses) and to perform simple communication tests with connected devices.

This product is a PCI Express bus-compatible interface board with support for bus master operation and which complies with IEEE-488.1 and IEEE-488.2. This product can be used in a PC to control communications with devices that support the GPIB interface and read GPIB bus line data.

The GPIB-F-LPE can also analyze the signal on the GPIB bus using the built-in memory (GPIB bus analyzer function).

This product supports a low-profile size slot and, if replaced with the supplied bracket, supports a standard size slot, too.

You can use the supplied driver library to develop application software using any programming language that supports the Win32 API routines (such as Visual Basic or Visual C++), or using LabVIEW.

- * The contents in this document are subject to change without notice.
- * Visit the CONTEC website to check the latest details in the document.
- * The information in the data sheets is as of August 2019.


Other

Supports both Low Profile size slots and standard size slots (use the supplied bracket as an adaptor).

Specifications

Item	GPIB-F-LPE	GPIB-FL-LPE
GPIB		
Number of channel	1 channel Conforms to IEEE-488.1, 488.2(GPIB) standards	
Transfer format	8-bit parallel, 3-wire handshake system	
Transfer rate	1.5Mbyte/sec	
Data buffer size	2Kbyte send, 2Kbyte receive	
Signal logic	Negative logic L level : 0.8V or less, H level : 2.0V or more	
Cable length between device	4m or less	
Total cable length	20m or less	
Connectable number of device	15 devices	
Analyzer buffer size	64K data points (1 data point : Control signals + DIO1 - 8)	None
Bus master section		
DMA channels	2 channels	
Transfer bus width	32-bit	
Transfer data length	8 PCI Words length (Max.)	
Transfer rate	80Mbyte/sec	
Scatter/Gather function	64Mbyte/ch	
Common section		
I/O address	Any 128-byte boundary	
Interrupt	1 level use	
Consumed current (Max.)	3.3VDC 600mA	
Operating conditions	0 - 50°C, 10 - 90%RH (No condensation)	
Bus specification	PCI Express Base Specification Rev. 1.0a x1	
External dimensions (mm)	121.69(L) x 67.90(H)	
Connector used	Micro ribbon connector (24-pin) 5555139-1 [made by AMP] or equivalent	
Weight	80g	

Board Dimensions



The standard outside dimension (L) is the distance from the end of the board to the outer surface of the slot cover.