


ハイヘリカルリーマ High helical Reamer



公差 (Tolerance)	D								d	
	0.01トビ ^h Increment 0.01	+0.005 0	2~2.6	+0.005 +0.001	2.7~5.9	+0.006 +0.002	6~17.5	+0.007 +0.003	17.6~20	+0.008 +0.004

右刃左ネジレ60° 食付角度 ~φ3.9まで2° φ3.91~1.5° SKH56

Helix Angle-Left60° Chamfer Angle ~φ3.9: 2° φ3.91: 1.5° HSS-Co.

直径 (ΦD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Center
2	5.7	15	20	60	2	2	60°凸
2.1	5.7	15	20	60	2.1	2	60°凸
2.2	5.7	15	20	60	2.2	2	60°凸
2.3	5.7	15	20	60	2.3	2	60°凸
2.4	5.7	15	20	60	2.4	2	60°凸
2.5	5.7	15	20	60	2.5	2	60°凸
2.6	5.7	15	20	60	2.6	2	60°凸
2.7	5.7	15	20	60	2.7	2	60°凸
2.8	5.7	15	20	60	2.8	2	60°凸
2.9	5.7	15	20	60	2.9	2	60°凸
3	5.7	22	23	70	3	2	60°凹
3.1	5.7	22	23	70	3.1	2	60°凹
3.2	5.7	22	23	70	3.2	2	60°凹
3.3	5.7	22	23	70	3.3	2	60°凹
3.4	5.7	22	23	70	3.4	2	60°凹
3.5	5.7	24	29	80	3.5	2	60°凹
3.6	5.7	24	29	80	3.6	2	60°凹
3.7	5.7	24	29	80	3.7	2	60°凹
3.8	5.7	24	29	80	3.8	2	60°凹
3.9	5.7	24	29	80	3.9	2	60°凹
4	6.55	24	29	80	4	2	60°凹
4.1	7.6	24	29	80	4.1	2	60°凹
4.2	7.6	24	29	80	4.2	2	60°凹
4.3	7.6	24	29	80	4.3	2	60°凹
4.4	7.6	24	29	80	4.4	2	60°凹
4.5	7.6	25	35	90	4.5	2	60°凹
4.6	7.6	25	35	90	4.6	2	60°凹
4.7	7.6	25	35	90	4.7	2	60°凹
4.8	7.6	25	35	90	4.8	2	60°凹
4.9	7.6	25	35	90	4.9	2	60°凹
5	7.6	25	35	90	5	2	60°凹
5.1	7.6	25	35	90	5.1	2	60°凹
5.2	7.6	25	35	90	5.2	2	60°凹
5.3	7.6	25	35	90	5.3	2	60°凹
5.4	7.6	25	35	90	5.4	2	60°凹
5.5	7.6	30	35	100	5.5	2	60°凹
5.6	7.6	30	35	100	5.6	2	60°凹
5.7	7.6	30	35	100	5.7	2	60°凹
5.8	7.6	30	35	100	5.8	2	60°凹
5.9	7.6	30	35	100	5.9	2	60°凹
6	7.6	30	35	100	6	3	60°凹
6.1	7.6	30	35	100	6.1	3	60°凹
6.2	9.5	30	35	100	6.2	3	60°凹
6.3	9.5	30	35	100	6.3	3	60°凹
6.4	9.5	30	35	100	6.4	3	60°凹
6.5	9.5	30	40	110	6.5	3	60°凹

直径 (ΦD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Center
6.6	9.5	30	40	110	6.6	3	60°凹
6.7	9.5	30	40	110	6.7	3	60°凹
6.8	9.5	30	40	110	6.8	3	60°凹
6.9	9.5	30	40	110	6.9	3	60°凹
7	9.5	30	40	110	7	3	60°凹
7.1	9.5	30	40	110	7.1	3	60°凹
7.2	9.5	30	40	110	7.2	3	60°凹
7.3	9.5	30	40	110	7.3	3	60°凹
7.4	9.5	30	40	110	7.4	3	60°凹
7.5	9.5	30	40	110	7.5	3	60°凹
7.6	9.5	30	40	110	7.6	3	60°凹
7.7	9.5	30	40	110	7.7	3	60°凹
7.8	9.5	30	40	110	7.8	3	60°凹
7.9	9.5	30	40	110	7.9	3	60°凹
8	9.5	35	50	125	8	3	60°凹
8.1	9.5	35	50	125	8.1	3	60°凹
8.2	9.5	35	50	125	8.2	3	60°凹
8.3	9.5	35	50	125	8.3	3	60°凹
8.4	9.5	35	50	125	8.4	3	60°凹
8.5	9.5	35	55	135	8.5	3	60°凹
8.6	9.5	35	55	135	8.6	3	60°凹
8.7	9.5	35	55	135	8.7	3	60°凹
8.8	9.5	35	55	135	8.8	3	60°凹
8.9	9.5	35	55	135	8.9	3	60°凹
9	9.5	35	55	135	9	3	60°凹
9.1	9.5	35	55	135	9.1	3	60°凹
9.2	9.5	35	55	135	9.2	3	60°凹
9.3	9.5	35	55	135	9.3	3	60°凹
9.4	9.5	35	55	135	9.4	3	60°凹
9.5	9.5	40	60	150	9.5	3	60°凹
9.6	9.5	40	60	150	9.6	3	60°凹
9.7	9.5	40	60	150	9.7	3	60°凹
9.8	9.5	40	60	150	9.8	3	60°凹
9.9	9.5	40	60	150	9.9	3	60°凹
10	9.5	40	60	150	10	3	60°凹
10.1	9.5	40	60	150	10.1	3	60°凹
10.2	9.5	40	60	150	10.2	3	60°凹
10.3	9.5	40	60	150	10.3	3	60°凹
10.4	9.5	40	60	150	10.4	3	60°凹
10.5	9.5	40	60	155	10.5	3	60°凹
10.6	9.5	40	60	155	10.6	3	60°凹
10.7	9.5	40	60	155	10.7	3	60°凹
10.8	9.5	40	60	155	10.8	3	60°凹
10.9	9.5	40	60	155	10.9	3	60°凹
11	9.5	40	60	155	11	3	60°凹
11.1	9.5	40	60	155	11.1	3	60°凹