


SANITARY PIPE

Material 304/316L



Sold cut is available

SIZE	D	C	t
8A	13.8	10.5	1.65
10A	17.3	14.0	1.65
15A	21.7	17.5	2.1
1S	25.4	23.0	1.2
1.25S	31.8	29.4	1.2
1.5S	38.1	35.7	1.2
2S	50.8	47.8	1.5
2.5S	63.5	59.5	2.0
3S	76.3	72.3	2.0
3.5S	89.1	85.1	2.0
4S	101.6	97.6	2.0




90° ELBOW WELD END

Material 304/316L



Long type is available

SIZE	D	A
1S	25.4	34
1.25S	31.8	38
1.5S	38.1	49
2S	50.8	61
2.5S	63.5	84
3S	76.3	89
3.5S	89.1	104
4S	101.6	133.4




45° ELBOW WELD END

Material 304/316L



SIZE	D	A
1S	25.4	15.8
1.25S	31.8	15.7
1.5S	38.1	23.7
2S	50.8	31.6
2.5S	63.5	42.0
3S	76.3	52.6
3.5S	89.1	42.9
4S	101.6	73.6




TEE WELD END

Material 304/316L



Low neck type and reduced type are available

SIZE	D	A
1S	25.4	34
1.25S	31.8	38
1.5S	38.1	49
2S	50.8	61
2.5S	63.5	84
3S	76.3	89
3.5S	89.1	104
4S	101.6	133.4




REDUCER WELD END (CONCENTRIC·ECCENTRIC)

Material 304/316L



SIZE	D1	D2	L
1.25S×1S	31.8	25.4	67
1.5S×1.25S	38.1	31.8	67
1.5S×1S	38.1	25.4	67
2S×1.5S	50.8	38.1	67
2S×1.25S	50.8	31.8	67
2S×1S	50.8	25.4	67
2.5S×2S	63.5	50.8	67
2.5S×1.5S	63.5	38.1	67
2.5S×1.25S	63.5	31.8	67
2.5S×1S	63.5	25.4	67
SIZE	D1	D2	L
3S×2.5S	76.3	63.5	67
3S×2S	76.3	50.8	67
3S×1.5S	76.3	38.1	67
3.5S×3S	89.1	76.3	67
3.5S×2.5S	89.1	63.5	67
3.5S×2S	89.1	50.8	67
4S×3.5S	101.6	89.1	102
4S×3S	101.6	76.3	102
4S×2.5S	101.6	63.5	102
4S×2S	101.6	50.8	102




CROSS WELD END

Material 304/316L



SIZE	D	A
1S	25.4	34
1.25S	31.8	38
1.5S	38.1	49
2S	50.8	61
2.5S	63.5	84
3S	76.3	89
3.5S	89.1	104
4S	101.6	133.4




180° BEND WELD END

Material 304/316L



SIZE	D	A	B
1.5S	38.1	152.4	76.2
2S	50.8	152.4	76.2
2.5S	63.5	190.6	95.3
3S	76.3	254	127
4S	101.6	254	127




HOSE ADAPTOR WELD END

Material 304/316L



SIZE	D	L
1S	25.4	60
1.25S	31.8	※
1.5S	38.1	80
2S	50.8	80
2.5S	63.5	80
3S	76.3	80
3.5S	89.1	※
4S	101.6	※



CAP

Material 304/316L



Dish-shaped is available

SIZE	D	A	t
1S	25.4	12.7	1.2
1.25S	31.8	15.9	1.2
1.5S	38.1	19.05	1.2
2S	50.8	25.4	1.5
2.5S	63.5	31.75	2.0
3S	76.3	38.15	2.0
3.5S	89.1	44.55	2.0
4S	101.6	50.8	2.0

