

GB-C D type C Series (Bushing Inner Diameter: 6 to 50 mm)

Designation of Part Number

GB-C **00** **00**

Bushing Length

Bushing I.D.

Product Symbol
(Material B1/8)

GB-C 0606

Please specify by part number.



Pb
Free

RoHS

ELV

Bushing I.D.	Recommended Dimension Mating Part		Bushing Dimensions								
	Housing I.D.	Shaft Dia.	O.D.	Wall Thickness	6	8	10	12	16	20	
6	$\phi 10H7^{+0.015}_0$	$\phi 6g6^{-0.004}_{-0.012}$	$\phi 6^{+0.028}_{+0.013}$	$\phi 10^{+0.021}_{+0.006}$	0606	0608	0610				
8	$\phi 14H7^{+0.018}_0$	$\phi 8g6^{-0.005}_{-0.014}$	$\phi 8^{+0.028}_{+0.013}$	$\phi 14^{+0.021}_{+0.006}$		0808	0810	0812	0816		
10	$\phi 16H7^{+0.018}_0$	$\phi 10g6^{-0.005}_{-0.014}$	$\phi 10^{+0.034}_{+0.016}$	$\phi 16^{+0.021}_{+0.006}$			1010	1012	1016	1020	
12	$\phi 18H7^{+0.018}_0$	$\phi 12g6^{-0.006}_{-0.017}$	$\phi 12^{+0.034}_{+0.016}$	$\phi 18^{+0.021}_{+0.006}$			1210	1212	1216	1220	
16	$\phi 22H7^{+0.021}_0$	$\phi 16g6^{-0.006}_{-0.017}$	$\phi 16^{+0.034}_{+0.016}$	$\phi 22^{+0.021}_{+0.006}$					1616	1620	
20	$\phi 30H7^{+0.021}_0$	$\phi 20g6^{-0.007}_{-0.020}$	$\phi 20^{+0.041}_{+0.020}$	$\phi 30^{+0.021}_{+0.006}$					2016	2020	
25	$\phi 35H7^{+0.025}_0$	$\phi 25g6^{-0.007}_{-0.020}$	$\phi 25^{+0.041}_{+0.020}$	$\phi 35^{+0.025}_{+0.009}$						2520	
30	$\phi 40H7^{+0.025}_0$	$\phi 30g6^{-0.007}_{-0.020}$	$\phi 30^{+0.041}_{+0.020}$	$\phi 40^{+0.025}_{+0.009}$						3020	
35	$\phi 45H7^{+0.025}_0$	$\phi 35g6^{-0.009}_{-0.025}$	$\phi 35^{+0.050}_{+0.025}$	$\phi 45^{+0.025}_{+0.009}$							
40	$\phi 50H7^{+0.025}_0$	$\phi 40g6^{-0.009}_{-0.025}$	$\phi 40^{+0.050}_{+0.025}$	$\phi 50^{+0.025}_{+0.009}$							
45	$\phi 55H7^{+0.030}_0$	$\phi 45g6^{-0.009}_{-0.025}$	$\phi 45^{+0.050}_{+0.025}$	$\phi 55^{+0.033}_{+0.011}$							
50	$\phi 62H7^{+0.030}_0$	$\phi 50g6^{-0.009}_{-0.025}$	$\phi 50^{+0.050}_{+0.025}$	$\phi 62^{+0.033}_{+0.011}$							