


2LS-BE ロングシャンクボールエンドミル 2枚刃

SINCE 1935
F.K.D.®

2LS-BE 2-Flute Long Shank Ball End Mills

材質=HSS-Co(SKH57)
刃数=2枚
リード角=右振り30°
刃径公差=0~-0.03
R公差=±0.025



○広範囲の金型加工に対応したロングタイプのボールエンドミル

●注文例=型番、R、数量 「4BE 2R」

Useful in wide range for the mold works. Inner radius and deep cut for long shank.

型番	R	刃径(D)	刃長(ℓ)	全長(L)	シャンク径(d)
2LS-BE	3	6	30	130	6
2LS-BE	3.25	6.5	35	130	6
2LS-BE	3.5	7	35	130	6
2LS-BE	3.75	7.5	35	130	8
2LS-BE	4	8	35	130	8
2LS-BE	4.25	8.5	40	130	8
2LS-BE	4.5	9	40	130	8
2LS-BE	4.75	9.5	40	130	10
2LS-BE	5	10	40	170	10
2LS-BE	5.25	10.5	45	170	10
2LS-BE	5.5	11	45	170	10
2LS-BE	5.75	11.5	45	170	12
2LS-BE	6	12	45	170	12
2LS-BE	6.25	12.5	50	170	12
2LS-BE	6.5	13	50	170	12
2LS-BE	6.75	13.5	50	170	12
2LS-BE	7	14	50	170	12
2LS-BE	7.25	14.5	55	170	12
2LS-BE	7.5	15	55	170	12
2LS-BE	7.75	15.5	55	170	16
2LS-BE	8	16	55	220	16
2LS-BE	8.25	16.5	60	220	16

型番	R	刃径(D)	刃長(ℓ)	全長(L)	シャンク径(d)
2LS-BE	8.5	17	60	220	16
2LS-BE	8.75	17.5	60	220	16
2LS-BE	9	18	60	220	16
2LS-BE	9.25	18.5	65	220	16
2LS-BE	9.5	19	65	220	16
2LS-BE	9.75	19.5	65	220	20
2LS-BE	10	20	65	260	20
2LS-BE	10.25	20.5	65	260	20
2LS-BE	10.5	21	65	260	20
2LS-BE	10.75	21.5	65	260	20
2LS-BE	11	22	65	260	20
2LS-BE	11.5	23	65	260	20
2LS-BE	12	24	70	260	20
2LS-BE	12.5	25	70	260	25
2LS-BE	13	26	70	260	25
2LS-BE	13.5	27	70	260	25
2LS-BE	14	28	75	260	25
2LS-BE	14.5	29	75	260	25
2LS-BE	15	30	75	260	25
2LS-BE	16	32	80	300	32
2LS-BE	20	40	100	320	32

被削材	鋳鉄	炭素鋼	合金鋼	工具鋼	調質鋼	ステンレス	アルミ合金	鋼合金	チタン合金	耐熱合金	樹脂
	FC.FCD	S50C	SCM	SKD	NAK	SUS304	Al	Cu	Ti6Al4V	インコネル	ABS
硬度	~350HB	~200HB	~250HB	~35HRC	~45HRC	~35HRC					ガラス繊維含まず
型番	○	○	○	○			○	○			○
2LS-BE	○	○	○	○			○	○			○