


ロングボールエンドミル Long Ball End Mill



公差 (Tolerance)	R			D	d		
	0.5~1.25	±0.01	1.3~16.5	±0.02	17~20	±0.05	±0.01

右刃右ネジレ35° 刃数:2 SKH57

Helix Angle-Right35° Number of Flute:2 HSS-Co.

寸法 R	刃径 (ΦD) <i>Dia.</i>	刃長 (ℓ) <i>Cut Length</i>	全長 (L) <i>Overall Length</i>	シャンク径 (Φd) <i>Shank Dia.</i>
0.5	1	6	60	6
0.55	1.1	6	60	6
0.6	1.2	8	60	6
0.65	1.3	8	60	6
0.7	1.4	8	60	6
0.75	1.5	8	60	6
0.8	1.6	10	60	6
0.85	1.7	10	60	6
0.9	1.8	10	60	6
0.95	1.9	10	60	6
1	2	10	60	6
1.5	3	15	70	6
2	4	20	80	6
2.5	5	20	90	6
3	6	25	100	6
3.5	7	30	120	8
4	8	30	120	8
4.5	9	35	120	8

寸法 R	刃径 (ΦD) <i>Dia.</i>	刃長 (ℓ) <i>Cut Length</i>	全長 (L) <i>Overall Length</i>	シャンク径 (Φd) <i>Shank Dia.</i>
5	10	40	130	10
5.5	11	40	130	12
6	12	40	130	12
6.5	13	45	130	12
7	14	45	130	12
7.5	15	50	130	12
8	16	60	150	16
8.5	17	65	160	16
9	18	65	160	16
9.5	19	65	160	16
10	20	80	170	20
10.5	21	80	170	20
11	22	90	180	20
12	24	100	190	20
12.5	25	100	190	25
15	30	120	210	25
17.5	35	130	250	32
20	40	130	250	32