

Dimensions [mm]

d1	d1- Tolerance ³⁾	d2	b1 h13	Part No.
32.0		37.0	25.0	JSM-3237-25
32.0		38.0	50.0	JSM-3238-50
35.0		39.0	20.0	JSM-3539-20
35.0		39.0	30.0	JSM-3539-30
35.0		39.0	40.0	JSM-3539-40
35.0	+0.050	39.0	50.0	JSM-3539-50
36.0	+0.150	40.0	45.0	JSM-3640-45
40.0		44.0	20.0	JSM-4044-20
40.0		44.0	30.0	JSM-4044-30
40.0		44.0	35.0	JSM-4044-35
40.0		44.0	40.0	JSM-4044-40
40.0		44.0	50.0	JSM-4044-50
42.0	+0.080 +0.240	46.0	73.0	JSM-4246-73
45.0	+0.025	50.0	20.0	JSM-4550-20
45.0	+0.125	50.0	30.0	JSM-4550-30
45.0		50.0	40.0	JSM-4550-40

d1	d1- Tolerance ³⁾	d2	b1 h13	Part No.
45.0	+0.025 +0.125	50.0	50.0	JSM-4550-50
50.0		55.0	20.0	JSM-5055-20
50.0		55.0	30.0	JSM-5055-30
50.0	+0.050	55.0	40.0	JSM-5055-40
50.0	+0.150	55.0	50.0	JSM-5055-50
50.0		55.0	60.0	JSM-5055-60
55.0		60.0	60.0	JSM-5560-60
60.0		65.0	60.0	JSM-6065-60
65.0		70.0	50.0	JSM-6570-50
70.0	+0.060	75.0	60.0	JSM-7075-60
75.0	+0.180	80.0	60.0	JSM-7580-60
80.0		85.0	100.0	JSM-8085-100
80.0		86.0	60.0	JSM-8086-60
100.0	+0.072	105.0	100.0	JSM-100105-100
110.0	+0.212	115.0	60.0	JSM-110115-60

³⁾ After press-fit. Testing methods ► Page 57



Couldn't find your size?

Do you need another length, other dimensions or tolerances? You need a particular design or alternative for your application? Please call us. igus® listens to your needs and provides you a solution very quickly.



Even more dimensions from stock

More than 300 dimensions are now available. Search online for your required bearing.

► www.igus.eu/iglidur-specialbearings