



ティー

UNION TEE



※印サイズの形状
※NS Type

単位：mm/Unit: mm

継手の呼び Part No.	適用管外径 Out. Dia. of Applied Pipe A		E	二面幅 Width across flats h	六角対辺 Hex Width H	I	ℓ	手締め(約) Fingertight Length (about) L	重量 Weight (kg)
	呼び径 Nominal sizes	外径 Out. Dia.							
※KTA04-000N		4	2.5	12	12	6	15	22.5	0.044
KTA06-000E		6	4	14	14	7	20	30.5	0.069
KTA08-000E		8	6	17	17	7	23	33.5	0.122
KTA10-000E		10	8	17	19	7	23	34.5	0.136
KTA12-000E		12	10	19	22	7	24	35.5	0.172
KTA15-000E		15	12	24	27	7.5	29	41.5	0.306
KTA16-000E		16	13	27	30	7.5	32	44.5	0.436
KTA18-000E		18	14	27	32	8	32	44.5	0.489
KTA20-000E		20	17	30	36	8	33	45.5	0.563
KTA22-000E		22	18	32	36	9	34	46.5	0.552
KTA25-000E		25	20	36	41	10	36	49.5	0.789
KTA28-000E		28	22	41	46	10	41	55	1.117
KTA30-000E		30	25	41	46	10	41	55.5	1.044
KTA35-000E		35	28	46	55	11	46	63.5	1.589
※KTA38-000N		38	32	50	60	12	50	69.5	2.052
※KTA40-000N		40	32	55	60	12	55	74.5	2.422
※KTA42-000N		42	34	55	60	12	55	74.5	2.276
※KTA50-000N		50	40	65	75	12	62	83.5	4.010
※KTA11-000N	1/8	10.5	8	17	19	7	23	34.5	0.132
※KTA13-000N	1/4	13.8	11	22	24	7.5	28	40	0.240
※KTA17-000N	3/8	17.3	14	27	32	8	32	44.5	0.452
※KTA21-000N	1/2	21.7	18	32	36	9	34	46.5	0.564
※KTA27-000N	3/4	27.2	22	41	46	10	41	55	1.127
※KTA34-000N	1	34.0	28	46	55	11	46	63.5	1.647
※KTA43-000N	1 1/4	42.7	34	60	65	12	57	77.5	3.022
※KTA48-000N	1 1/2	48.6	40	65	75	12	62	83.5	4.059

注. 予告なしに、品質・性能・改善のため寸法を変更する事があります。

Note. Dimensions might be modified due to improvement of quality and performance.