

NF / F / NV / V CAST IRON SPOKED HANDWHEELS



NF

(Straight-Spoke
Without Handle-Mounting
Tapped Hole)



F

(Straight-Spoke
With Handle-Mounting Tapped Hole)
Note : Handle must be ordered separately.



NF NV 355~
Protection Cap




(Angle-Spoke
Without Handle-Mounting
Tapped Hole)




V


(Angle-Spoke
With Handle-Mounting Tapped Hole)
Note : Handle must be ordered separately.



NF F 80~315
(Straight-Spoke)



NV V 80~315
(Angle-Spoke)



Protection Cap Hex. Socket Setscrew

F V 355~500 **NF NV** 355~500

Handwheel
Cast iron
Chrome plated

NF F (Straight-Spoke)

Part Number		No. of Spokes	A	B	C	D	E	F	For F Type		Weight (g)
Without Handle-Mounting Tapped Hole	With Handle-Mounting Tapped Hole								G	H	
NF 80	F 80	3	80	24	25	24	14	9	30	M 5×0.8	350
NF100	F100		100	25	30	25	15		40		500
NF125	F125		125	29	35	29	16	12	51		M 6×1
NF140	F140		140	30		30	17		58	1,150	
NF160	F160		160	33	38	33	18	13	67	M 8×1.25	1,500
NF180	F180		180	35		35	20		76		1,600
NF200	F200		200	37	40	37	22	84	2,200		
NF225	F225	5	225	39	45	39	24	14	95	M10×1.5	2,900
NF250	F250		250	41		41	26		107		3,700
NF280	F280		280	43	53	43		122	4,500		
NF315	F315		315	45	60	45	28	16	138	M12×1.75	5,900
NF355	F355		355	50	67	50	30		151		7,800
NF400	F400		400	52		52	32	19	172	M16×2	9,600
NF450	F450		450	60	72	34	23		196		12,800
NF500	F500	500	82		221			14,000			