


Adapter KHA



unit: mm

Part No.	Tube OD A	(R) T	Minimum Opening E	Gauge Length G	Hex. H	ℓ_1	ℓ_2	Approx. L	Weight (kg)
KHA06-010CE	6	$\frac{1}{8}$	3	3.97	10	19	5	30	0.011
KHA06-020CE	6	$\frac{1}{4}$	3	6.01	14	19	7	34	0.024
KHA08-010CE	8	$\frac{1}{8}$	4	3.97	10	19	5	30	0.013
KHA08-020CE	8	$\frac{1}{4}$	5	6.01	14	19	7	34	0.025
KHA10-020CE	10	$\frac{1}{4}$	6	6.01	14	19	7	34	0.026
KHA10-030CE	10	$\frac{3}{8}$	6	6.35	17	19	7	34.6	0.039
KHA12-020CE	12	$\frac{1}{4}$	8	6.01	14	20	7	35	0.026
KHA12-030CE	12	$\frac{3}{8}$	8	6.35	17	20	7	35.7	0.039
KHA16-030CE	16	$\frac{3}{8}$	9	6.35	17	24	7	39.7	0.044
KHA16-040CE	16	$\frac{1}{2}$	11	8.16	22	24	8	42.8	0.070
KHA20-040CE	20	$\frac{1}{2}$	12	8.16	22	26	8	44.8	0.090
KHA20-060CE	20	$\frac{3}{4}$	14	9.53	27	26	10	47.5	0.128
KHA25-060CE	25	$\frac{3}{4}$	16	9.53	27	28	10	49.5	0.133
KHA25-080CE	25	1	18	10.39	36	28	11	52.6	0.221
KHA30-060CE	30	$\frac{3}{4}$	16	9.53	32	28	10.5	50	0.218
KHA30-080CE	30	1	22	10.39	36	28	11	52.6	0.221
KHA30-100CE	30	$\frac{3}{4}$	22	12.7	46	28	12	54.3	0.420