


SSS・SSF・SPA ねじ込み形管継手 / Threaded Pipe Fittings

メスオスソケットB形 SSS / Street Socket Type B SSS




単位: mm / unit: mm

継手の呼び Part No.	T ₁ × T ₂ (R × Rc)	d	L	H (六角) H (HEX)	重量 (kg) Weight (kg)
SSS02-030J	1/4 × 3/8	7	35	24	0.064
SSS03-040J	3/8 × 1/2	9	41	32	0.15
○ SSS04-060J	1/2 × 3/4	12	48	36	0.20
○ SSS06-080J	3/4 × 1	16	55	46	0.39
○ SSS08-100J	1 × 1 1/4	20	64	55	0.63
○ SSS10-120J	1 1/4 × 1 1/2	28	69	65	0.94
○ SSS12-160J	1 1/2 × 2	32	75	75	1.31

○P処理品 / Parkerizing


メスオスソケットC形 SSF / Street Socket Type C SSF



単位: mm / unit: mm

継手の呼び Part No.	T ₁ (G)	T ₂ (Rc)	d	K	ℓ ₁	L	H (六角) H (HEX)	O- Ring	重量 (kg) Weight (kg)
SSF02-020J	1/4	1/4	6	19	12	33	22	P11	0.061
SSF03-030J	3/8	3/8	8	22	12	35	24	P14	0.076
SSF04-040J	1/2	1/2	12	27	14	42	32	P18	0.16
SSF06-060J	3/4	3/4	16	36	16	47	36	P24	0.21
SSF08-080J	1	1	22	41	18	55	46	P29	0.40
SSF10-100J	1 1/4	1 1/4	28	50	20	63	55	P38	0.64
SSF12-120J	1 1/2	1 1/2	31	55	21	66	65	P44	0.96
SSF16-160J	2	2	36	75	25	76	75	P56	1.39

六角穴付プラグ SPA / Hollow hex Plug SPA



単位: mm / unit: mm

継手の呼び Part No.	T (R)	H	L	A	重量 (kg) Weight (kg)
◆ SPA01-000J	1/8	5	7	0.45	0.003
◆ SPA02-000J	1/4	6	9	0.7	0.008
◆ SPA03-000J	3/8	8	10	0.7	0.012
◆ SPA04-000J	1/2	10	12	0.9	0.024
◆ SPA06-000J	3/4	14	14	0.9	0.041
◆ SPA08-000J	1	17	16.5	1.1	0.088
◆ SPA10-000J	1 1/4	22	19	1.1	0.14
◆ SPA12-000J	1 1/2	22	20	1.1	0.23
◆ SPA16-000J	2	27	22	1.1	0.35

◆黒染 / Triiron tetraoxide

材質: 炭素鋼 / Material: S45C or S25C
Aは基準径の位置を示す。 / A indicates the position of standard bore