


ユニオン SUA / Union SUA




単位: mm / unit: mm

継手の呼び Part No.	T (Rc)	N (八角) N (OCT)	L	H (八角) H (OCT)	S	O-Ring	重量 (kg) Weight (kg)
SUA02-000J	1/4	20	39.5	36	M30×2	P18	0.17
SUA03-000J	3/8	24	41.5	41	M36×2	P20	0.23
SUA04-000J	1/2	29	49	46	M39×2	G25	0.33
SUA06-000J	3/4	35	55	55	M48×2	G30	0.54
SUA08-000J	1	44	59.5	65	M56×2	G35	0.80
SUA10-000J	1 1/4	54	67.5	80	M68×2	G45	1.34
SUA12-000J	1 1/2	60	79	85	M72×2	G50	1.74
SUA16-000J	2	75	82	104	M90×2	G65	2.55

注) O-RingはJIS B2401-1Bです。定格圧力:21MPa(210kgf/cm²)
 使用温度:120℃以下
 炭素鋼以外は寸法が異なるので、都度お問い合わせください。(Jシリーズになります。)
 Note: O-ring is JIS B2401-1B. Rated pressure: 21MPa (210kgf/cm²)
 Operating temperature: Less than 120℃
 Stainless steel products deviate from the above dimensions. (contact us)

ユニオンF形 WUF / Union Type F WUF



単位: mm / unit: mm

継手の呼び Part No.	呼び径 Nominal sizes	B	C	D	M	L	N(八角) N (OCT)	H(八角) H (OCT)	S	T (R)	O-Ring	重量 (kg) Weight (kg)
WUF02-020J	1/4	14.3	10	9.4	22	39	20	36	M30×2	1/4	P18	0.18
WUF03-030J	3/8	17.8	10	12.7	27	41	24	41	M36×2	3/8	P20	0.23
WUF04-040J	1/2	22.2	10	16.1	32	48	29	46	M39×2	1/2	G25	0.33
WUF06-060J	3/4	27.7	13	21.4	38	54	35	55	M48×2	3/4	G30	0.54
WUF08-080J	1	34.5	13	27.2	47	58.5	44	65	M56×2	1	G35	0.80
WUF10-100J	1 1/4	43.2	13	35.5	58	66.5	54	80	M68×2	1 1/4	G45	1.36
WUF12-120J	1 1/2	49.1	13	41.2	63	78	60	85	M72×2	1 1/2	G50	1.77
WUF16-160J	2	61.1	16	52.7	81	79	75	104	M90×2	2	G65	2.58

注) O-RingはJIS B2401-1Bです。定格圧力:21MPa(210kgf/cm²)
 使用温度:120℃以下
 炭素鋼以外は寸法が異なるので、都度お問い合わせください。(Jシリーズになります。)
 Note: O-ring is JIS B2401-1B. Rated pressure: 21MPa (210kgf/cm²)
 Operating temperature: Less than 120℃
 Stainless steel products deviate from the above dimensions. (contact us)