



WPF

隔壁メスユニオン

Bulkhead female union

黄銅製

Brass



部品番号 PART NO.	適用チューブ 外径 TUBE O.D. TO BE USED (mm)	T (Rc)	六角 対辺 HEX (mm)		L ₁ (mm)	L ₂ (mm)	K 最大パネル厚 MAX. PANEL THICKNESS (mm)	M×P (mm)	IN (mm)	重量 WEIGHT (g)	最小内径 ORIFICE (mm)	有効断面積 EFFECTIVE SECTIONAL AREA (mm ²)	
			S ₁	S ₂								ナイロンチューブ NYLON TUBE	ウレタンチューブ POLYURETHANE TUBE
WPF-06-01	6	1/8	19	19	28.0	10	10	16X1	17	42	4	5.3	5.3
WPF-06-02	6	1/4	19	19	29.0	14	10	16X1	17	46	4	5.3	5.3
WPF-08-02	8	1/4	22	22	32.5	14	10	17X1	18	60	6	26.9	18.0
WPF-08-03	8	3/8	22	22	34.0	15	10	17X1	18	57	6	26.9	18.0
WPF-10-02	10	1/4	24	24	33.5	14	12	20X1	19	72	8	42.9	30.0
WPF-10-03	10	3/8	24	24	36.0	15	12	20X1	19	75	8	42.9	30.0
WPF-12-02	12	1/4	27	27	36.0	15	13	24X1	21	102	8	60.0	45.0
WPF-12-03	12	3/8	27	27	37.0	15	13	24X1	21	107	8	60.0	45.0
WPF-12-04	12	1/2	27	27	39.0	18	13	24X1	21	120	10	60.0	45.0



WU

ユニオン

Union

樹脂製

Plastic body



部品番号 PART NO.	適用チューブ 外径 TUBE O.D. TO BE USED (mm)	φD (mm)	L (mm)	IN (mm)	重量 WEIGHT (g)	最小内径 ORIFICE (mm)	有効断面積 EFFECTIVE SECTIONAL AREA (mm ²)	
							ナイロンチューブ NYLON TUBE	ウレタンチューブ POLYURETHANE TUBE
WU-06P	6	14	36	17	5	4	8.8	8.8
WU-08P	8	17	38	18	7	6	25.4	19.0
WU-10P	10	19	42	19	15	8	42.9	34.5
WU-12P	12	22	44	21	25	10	59.9	50.5



WU

ユニオン

Union

黄銅製

Brass



部品番号 PART NO.	適用チューブ 外径 TUBE O.D. TO BE USED (mm)	φD (mm)	L (mm)	IN (mm)	重量 WEIGHT (g)	最小内径 ORIFICE (mm)	有効断面積 EFFECTIVE SECTIONAL AREA (mm ²)	
							ナイロンチューブ NYLON TUBE	ウレタンチューブ POLYURETHANE TUBE
WU-06BS	6	14	39	17	26	4.0	13.1	13.1
WU-08BS	8	16	40	18	33	6.0	26.1	19.0
WU-10BS	10	18	42	19	40	7.5	42.0	40.0
WU-12BS	12	22	46	20	68	9.0	58.0	46.0