





SUS50A

● Order No. Example



- ChainNo.50
- Chain Pitch(P)15.875mm
- Roller Link Inner Width(W) 9.53 mm
- Roller Outside Diameter(Dr)10.16 mm
- Tooth Width(T) 8.7 mm

 Stainless Steel  304

| Type | No. of Teeth | Outer Diameter Do | Pitch Diameter Dp | Shaft Hole Diameter d | | Weight kg | ¥ | Semi-F ¥ |
|------------|--------------|-------------------|-------------------|-----------------------|---------|-----------|---|----------|
| | | | | Prepared Hole Product | Minimum | | | |
| SUS 50A | 10 | 58 | 51.37 | 10 | 11 | 0.14 | | |
| | 11 | 64 | 56.35 | 12 | 13 | 0.17 | | |
| | 12 | 69 | 61.34 | 12 | 13 | 0.20 | | |
| | 13 | 74 | 66.34 | 12 | 13 | 0.23 | | |
| | 14 | 79 | 71.34 | 12 | 13 | 0.27 | | |
| | 15 | 84 | 76.35 | 12 | 13 | 0.30 | | |
| | 16 | 89 | 81.37 | 14 | 15 | 0.35 | | |
| | 17 | 94 | 86.39 | 14 | 15 | 0.40 | | |
| | 18 | 100 | 91.42 | 14 | 15 | 0.45 | | |
| | 19 | 105 | 96.45 | 14 | 15 | 0.48 | | |
| 20 | 110 | 101.48 | 14 | 15 | 0.50 | | | |
| 21 | 115 | 106.51 | 14 | 15 | 0.60 | | | |
| 22 | 120 | 111.55 | 16 | 17 | 0.66 | | | |
| 23 | 125 | 116.58 | 16 | 17 | 0.72 | | | |
| 24 | 130 | 121.62 | 16 | 17 | 0.78 | | | |