



# FBK60B

## ● Order No. Example

**FBK 60B 20 D25**



- Chain .....No.60
- Chain Pitch .....(P)19.05mm
- Roller Link Inner Width .....(W)12.70mm
- Roller Outside Diameter .....(Dr)11.91mm
- Tooth Width .....(T)11.7 mm

| Type           | No. of Teeth | Outer Diameter Do | Pitch Diameter Dp | Boss Diameter BD | Boss Length BL | a  | Weight kg | φD <sup>H7</sup>     | ¥ |
|----------------|--------------|-------------------|-------------------|------------------|----------------|----|-----------|----------------------|---|
| <b>FBK 60B</b> | 10           | 68                | 61.65             | ★49              | 32             | 6  | 0.49      | 25                   |   |
|                | 11           | 76                | 67.62             | ★51              | 32             | 6  | 0.60      | 25 28 30             |   |
|                | 12           | 83                | 73.60             | 51               | 32             | 8  | 0.69      | 24 25 28 30          |   |
|                | 13           | 89                | 79.60             | 57               | 32             | 8  | 0.81      | 25 28 30             |   |
|                | 14           | 95                | 85.61             | 62               | 32             | 8  | 0.96      | 20 25 28 30          |   |
|                | 15           | 101               | 91.62             | 68               | 32             | 8  | 1.10      | 18 24 25 28 30       |   |
|                | 16           | 107               | 97.65             | 73               | 32             | 8  | 1.30      | 24 25 28 30          |   |
|                | 17           | 113               | 103.67            | 73               | 32             | 8  | 1.40      | 25 28 30             |   |
|                | 18           | 119               | 109.71            | 83               | 40             | 12 | 2.00      | 25 28 30             |   |
|                | 19           | 126               | 115.74            | 83               | 40             | 12 | 2.10      | 25 28 30 32 35 38    |   |
|                | 20           | 132               | 121.78            | 83               | 40             | 12 | 2.20      | 25 28 30 32 35 38 40 |   |
|                | 21           | 138               | 127.82            | 83               | 40             | 12 | 2.30      | 25 28 30             |   |
|                | 22           | 144               | 133.86            | 83               | 40             | 12 | 2.50      | 28 30 35 40          |   |
|                | 23           | 150               | 139.90            | 83               | 40             | 12 | 2.50      | 28 30                |   |
|                | 24           | 156               | 145.95            | 83               | 40             | 12 | 2.60      | 25 30 35 38 40       |   |
|                | 25           | 162               | 151.99            | 83               | 40             | 12 | 2.70      | 28 30 35 40          |   |
|                | 26           | 168               | 158.04            | 83               | 40             | 12 | 2.90      | 30 35                |   |
|                | 27           | 174               | 164.09            | 83               | 40             | 12 | 3.00      | 30 35 40             |   |
|                | 28           | 180               | 170.14            | 83               | 40             | 12 | 3.10      | 30 35 40             |   |
|                | 30           | 193               | 182.25            | 83               | 40             | 12 | 3.40      | 35 40                |   |