

# CKA·CKB·CKD Series Standard Chuck

## Light-Weight and Compact Basic Model

### Key Features

- **No adjustment for multi-purpose application**  
Long motion stroke for multi-purpose use
- **3 types available for various types of application**  
3-Jaw = CKA, 2-Jaw = CKB, and 4-Jaw = CKD
- **Compact and powerful**  
Light-weight compact design but with high grip force



CKA-50MS

Chuck  
(2, 3, & 4-Jaw)

### How To Order

Standard ----- **CKA-15AS**

Option ----- **CKA - 20AS - ET3LS2 - FE** ----- Iron body CKA-20AS with 2 of ET3L non-contact reed switches

Model		Size		Sensor, Quantity		Option			
Symbol	Symbol	Symbol	Name	Symbol	Name	Symbol	Name	Symbol	Name
CKA	15AS <sup>*1</sup>	ET3 <sup>*2</sup>	Non-Contact 3-Lead	S1	1 Sensor	NO	Normally Open		
CKB	20AS	ET3L <sup>*3</sup>	Non-Contact 3-Lead	S2	2 Sensors	NC	Normally Closed		
CKD	25AS	ET2 <sup>*2</sup>	Non-Contact 2-Lead			FE	Iron Body		
	30AS	ET2L <sup>*3</sup>	Non-Contact 2-Lead			H <sup>*5</sup>	Low Pressure Hydraulic		
	40AS	E24 <sup>*3</sup>	Contact 2-Lead			SU	Stainless Steel for Iron Material		
	50MS	E24L <sup>*3</sup>	Contact 2-Lead			SUA	All Stainless Steel		
	60MS	E25 <sup>*3</sup>	Contact 2-Lead			T	Heat-Proof		
	70MS	E25L <sup>*3</sup>	Contact 2-Lead			W <sup>*5</sup>	Spring Pusher		

<sup>\*1</sup> CKA only

For sensor detail ▶ 277P

For option detail ▶ 36P