


80A

● Order No. Example

80A 20

Type No. of Teeth
Sprocket No.



- ChainNo.80
- Chain Pitch(P)25.4 mm
- Roller Link Inner Width(W)15.88mm
- Roller Outside Diameter(Dr)15.88mm
- Tooth Width(T)14.6 mm

 Common Steel

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole	Minimum			
80A	10	93	82.19	15	16	0.60		
	11	102	90.16	15	16	0.73		
	12	110	98.14	15	16	0.83		
	13	118	106.14	16	17	1.00		
	14	127	114.15	16	17	1.16		
	15	135	122.17	20	21	1.30		
	16	143	130.20	20	21	1.50		
	17	151	138.23	20	21	1.70		
	18	159	146.27	20	21	1.90		
	19	167	154.32	20	21	2.10		
	20	176	162.37	20	21	2.35		
	21	184	170.42	20	21	2.57		
	22	192	178.48	26	27	2.82		
	23	200	186.54	26	27	3.10		
	24	208	194.60	26	27	3.35		
	25	216	202.66	26	27	3.65		
	26	224	210.72	26	27	3.95		
	27	233	218.79	26	27	4.25		
	28	241	226.86	26	27	4.60		
	29	249	234.93	26	27	4.93		
	30	257	243.00	26	27	5.30		
	31	265	251.07	26	27	5.63		
	32	273	259.14	26	27	6.00		
	33	281	267.21	26	27	6.40		
	34	289	275.29	26	27	6.80		
	35	297	283.36	26	27	7.20		
	36	306	291.43	26	27	7.60		
	37	314	299.51	26	27	8.00		
	38	322	307.58	26	27	8.50		
	39	330	315.66	26	27	8.90		