


SRWS Triwing Pan Head Machine Screws



WEB Selection Tool WEB CAD Download Tamper Resistance SUS Stainless steel



● Part number specification

SRWS-M5-16



Order in number of packs.
The minimum order quantity is 1 piece. → P.794

- They cannot be installed or removed by using standard tools.
- Install and remove by **SRWB** Specialty Bits and **SRD** Specialty Magnetic Screwdriver together.

● Application

Machinery, tools, equipment, and devices disassembly prevention - tampering prevention, theft prevention for outdoor facilities, security measures, and safety measures

● Material/Finish



	SRWS
Main Body	SUS304
Strength Class	Equivalent to A2-50

Unit : mm

Part Number	M	L			D1	L1	Bit Part No.	Screwdriver Part No.	Mass (g)
SRWS-M3	M3	6	8	10	5.6	1.8	SRWB-2	SRD-6.35	0.54 - 0.7
SRWS-M4	M4		8	10	8.2	2.9	SRWB-4	SRD-6.35	1.5 - 1.9
SRWS-M5	M5			10	9.5	3.4	SRWB-5	SRD-6.35	2.8 - 3.5


Part Number	Qty*1 per pack
SRWS-M3	20
SRWS-M4	20
SRWS-M5	20

*1 The minimum order quantity is 1 piece. → P.794

● **SRWB** Dedicated bit

Unit : mm


Part Number	L	B	Mass (g)	Qty per pack
SRWB-2	25.4	6.35	4.2	1
SRWB-4	25.4	6.35	5.2	1
SRWB-5	25.4	6.35	5.6	1



● **SRD** Dedicated magnet screwdriver

Unit : mm

Part Number	L	B	Mass (g)	Qty per pack
SRD-6.35	210	6.35	98	1



1 Individual Sales → P.794 Cleanroom Wash & Packaging → P.792 Screw Length Adjustment → P.796 Vibration Resistant → P.795 Modification process for captive use → P.791
Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge