


# SAK-A / SAK-B Block for Adjust Bolt




WEB Selection Tool    WEB CAD Download

## SAK-A



## SAK-B



- Block for fixing Adjust bolt **SAT**.
- You can choose it from the following two types according to your application. **3**
  - SAK-A** — Mounting from above
  - SAK-B** — Mounting from front
- Please combine with the adjust bolt **SAT**.
  - ➔ P.539

- Material/Finish

RoHS Compliant

	SAK-A / SAK-B
Main body	SS400 Nickel Plating

### SAK-A Mounting from above

Unit : mm

Part Number	Nominal <b>1</b>	H <b>2</b>	A	H <sub>1</sub>	P	W	d	R	C	Lc	Mass (g)		
SAK-6-A	6	10	20	30	9	6	20	32	5.5	4.5	8	4.4	28 - 60
SAK-8-A	8	10	20	30	12	8	26	38	7.5	5.5	9.5	5.4	49 - 113
SAK-10-A	10	15	30	16	10	32	50	9.5	9	14	8.6	8.6	117 - 200
SAK-12-A	12	15	30	19	11	40	65	11.5	9	14	8.6	8.6	197 - 329

### SAK-B Mounting from front

Unit : mm

Part Number	Nominal <b>1</b>	H	A	H <sub>1</sub>	H <sub>2</sub>	P	W	d	d <sub>1</sub>	Mass (g)
SAK-6-B	6	25	9	6	5	20	32	5.5	6	62
SAK-8-B	8	25	12	8	6	26	38	7.5	7	102
SAK-10-B	10	35	16	10	9	32	50	9.5	9.5	186
SAK-12-B	12	40	19	11	12	40	65	11.5	11.5	293

- Part number specification

**SAK-10-30-A** (For **SAK-A**)

Product Code **1** **2** **3**

**SAK-8-B** (For **SAK-B**)

Product Code **1** **3**

Cleanroom Wash & Packaging ➔ P.792	Screw Combination ➔ P.798	Screw Length Adjustment ➔ P.796	Vibration Resistant ➔ P.795
Not Available	Not Available	Not Available	Not Available