



# Handles D and T Blades



## NG-3 Handle NG3000

NogaGrip-3 - holds all blade holders.  
Designed for maximum comfort in your hand.




## YT Handle YT1000

The perfect grip for Noga adjustable scrapers,  
needle files, pins and drills. Range: 2.2-4.5mm



## SC Handle SC1300

Hexagonal black anodized 12 mm diameter  
handle with knurled locking collar for blade  
extension control. - holds D50, D66, D75, D77  
and T80 scraper blades. Length 120 mm.



## H.D. SC Handle SC1400

Hexagonal black anodized 14 mm diameter  
handle with knurled locking collar for blade  
extension control. Holds T120 scraper blade  
and screw bits. Length 130 mm.



BLADES	order no.		width x length (mm)	angle (degrees)	package weight (g)	package quantity
<b>D50</b>	BD5010		2.5 x 50	60	37	10
<b>D50TiN</b>	BD5012		2.5 x 50	60	37	10
<b>D55 Carbide</b>	BD5501		2.5 x 50	60	9	1
<b>D66</b>	BD6610		2.7 x 50	50	44	10
<b>D75</b>	BD7501		2.5 x 75	60	8	1
<b>D77</b>	BD7701		2.7 x 75	50	9	1
<b>T40</b>	BT4001		4.2 x 40	60	7	1
<b>T60</b>	BT6001		7.4 x 60	60	11	1
<b>T80</b>	BT8001		4.2 x 80	60	11	1
<b>T120</b>	BT1200		7.4 x 120	60	24	1

All blades are made of H.S.S. Hardness 62-64Rc, except D55 Carbide 1400-1700 HV and T80, T120 CR115 58-60Rc

## D Holder EL05003

Holds D scraper blades. A 3 mm setscrew - holds the  
blade in position. Allen key included. Length 131 mm.



## TN Holder EL0608

Holds T40 and T60 scraper blades.  
NF10 Int. thread. Length 113 mm.

