




ANGLE

07

LEVELNIC DATA SYSTEM

Enables data display and saving of up to 8 levelnic with one PC



Example using multiple units with Bluetooth wireless communication

- USE** • For data management of multiple Levelnics
- MATERIALS** • Body: Stainless steel
- FEATURES** • 8 Levelnics can be connected at once
 - Data display software included
- SPECIFICATIONS**

| Order No. | Model No. | Weight |
|-----------|-----------|--------|
| 010037 | DL-ADP | 1.6kg |

| | |
|-----------------------|---|
| Input | D-SUB (9 pins, male) RS-232C compliant, 8 inputs (For Levelnic connection only) 1200 Baud, 1 stop bit, No parity, No handshaking |
| Output | D-SUB (9 pins, male) RS-232C compliant, 1 output (PC connection) 9600 Baud, 1 stop bit, No parity No Hardware handshaking |
| Operating Temperature | 0 ~ 40°C |
| Power Source | AC100V Adapter [DC9V Output] (Included) AAA batteries (1.5V) 6 pc ※ Run time depends on number of Levelnics |
| Dimensions | W180 × H150 × D130mm |
| Applicable Levelnic | DL-S3, DL-S3C, DL-S3L, DL-m3, DL-m3LS, DL-S2W ※ DL-P5AD, DL-P6 can also use cable connection ※ DL-S2W, DL-BW can connect using built-in wireless capability |

LEVELNIC DISPLAY

Can display data at a distance of 50-100m (line-of-sight). Enables measurement process to be done by one person. The work of two can be done by one person.



Combination example with DL-S2W

- USE** • Levelnic measurement data display
- MATERIALS** • Body: Stainless steel
- FEATURES** • Can divide measurement value into half with one-touch operation (DL-S2W only)
- SPECIFICATIONS**

| Order No. | Model No. | Weight |
|-----------|-----------|--------|
| 010024 | DL-D4 | 330g |

| | |
|---------------------------|--|
| Display Range | As per Levelnic spec. |
| Minimum Reading | As per Levelnic spec. |
| Operating Temperature | 0 ~ 40°C |
| Input Signal | Conforms to RS-232C (Levelnic digital output signal only) |
| Power Source | " 9V " type dry cell / AC adapter (included) |
| Run time (Continuous use) | with wireless connection : Alkaline cell : Approx. 5 hrs with cable connection : Alkaline cell : Approx. 60 hrs ※ May vary depending upon measurement conditions |
| Dimensions | L116 × W62 × H48mm |
| Applicable Levelnic | DL-S3, DL-S3C, DL-S3L, DL-m3, DL-m3LS, DL-S2W ※ DL-P5AD, DL-P6 can also use cable connection ※ Can connect to Wireless such as DL-S2W, DL-BW |

ANGLE

LEVELNIC

PRECISION
LEVEL

ANGLE
LEVEL

LEVEL

PROTRACTOR