


Stainless nut



*The inch size type has no cut.


●Millimeter size type (Group 4)

Product number	Applicable tube outer diameter (mm)	T Thread size (M)	L (mm)	H ₂ Width across flat (mm)	Weight (g)
N6-S	6	M10×1.0	9.0	12.0	5.0
N8-S	8	M12×1.0	9.0	14.0	6.0
N10-S	10	M15×1.0	10.0	17.0	9.0
N12-S	12	M17×1.0	11.0	19.0	11.0

●Inch size type (Group 1)

Product number	Applicable tube outer diameter (inch)	T Thread size (M)	L (mm)	H ₂ Width across flat (mm)	Weight (g)
N1/4-S	1/4	M10×1.0	9.0	12.0	5.0
N5/16-S	5/16	M12×1.0	9.0	14.0	6.0
N3/8-S	3/8	M14×1.0	10.0	17.0	10.0
N1/2-S	1/2	M17×1.0	11.5	19.0	11.0

Nylon sleeve



●Millimeter size type (Color: milky white)

Product number	Applicable tube outer diameter (mm)	L (mm)
SN6	6	11.0
SN8	8	11.0
SN10	10	12.0
SN12	12	13.0

●Inch size type (Color: black)

Product number	Applicable tube outer diameter (inch)	L (mm)
SN1/4	1/4	11.0
SN5/16	5/16	11.0
SN3/8	3/8	12.0
SN1/2	1/2	13.0

Tube

Clean tube

Processed tube

PushOne fitting

QuickSeal fitting

Clean fitting/Chemifit

Bamboo-shoot fitting

Control switch/Detachable series

Jig/Tool/Accessory

Technical information

Reference