


TH1047 G-LIST No

LONG SHANK・WITH INTERRUPTED THREADS インターラップ形 ロングシャンク

EX-LT-IRT



●マークの説明はP.2をご覧ください。 See page 2 for explanation of icons.

ねじの種類：PT(Rc)

単位:mm Unit:mm

ツールNo. EDP NO.	呼び Thread Size	精度 TAP Limit	食付 ℓc	全長 L	ねじ長 ℓ	軽径 ℓg	シャンク径 Ds	溝数 Flutes	在庫 Stock	重量 Weight	標準価格 (Yen)
15710	1/8 - 28	JIS2	2.5P	120	19	13	8	5	D	51	8,120
15711				150						63	11,000
15715	1/4 - 19	JIS2	2.5P	120	28	21	11	5	D	87	9,370
15716				150						113	11,700
15720				120						140	15,000

■突き出しセンチ長さ・シャンク四角部寸法 ℓk , K はP.890をご覧ください。

1. タップ精度はめねじ精度を保証するものではありません。
2. 切削油剤、ペーストはP.868をご参照下さい。

ツールNo. EDP NO.	呼び Thread Size	精度 TAP Limit	食付 ℓc	全長 L	ねじ長 ℓ	軽径 ℓg	シャンク径 Ds	溝数 Flutes	在庫 Stock	重量 Weight	標準価格 (Yen)
15721	3/8 - 19	JIS2	2.5P	150	28	21	14	5	D	181	18,900
15725	1/2 - 14			150	35	25	18			280	23,000
15733	3/4 - 14			150	35	25	23			460	36,700
15741	1 - 11			150	45	32	26			613	55,200

■ Please see page 890 for length of external centre and shank square length ℓk and width K .

1. TAP Limit does not guarantee thread limit for the internal thread after tapping.
2. Cutting fluid and Paste : Please refer to P.868.

SPECIFICATION CHART
形状寸法表

TAPS
タップ

TAPER PIPE THREAD TAP SERIES
管用テーパタップシリーズ

TH1048 G-LIST No

LONG SHANK・WITH INTERRUPTED THREADS (SHORT THREAD) インターラップ形短ねじ ロングシャンク

EX-LT-S-IRT



●マークの説明はP.2をご覧ください。 See page 2 for explanation of icons.

ねじの種類：PT(Rc)

単位:mm Unit:mm

ツールNo. EDP NO.	呼び Thread Size	精度 TAP Limit	食付 ℓc	全長 L	ねじ長 ℓ	軽径 ℓg	シャンク径 Ds	溝数 Flutes	在庫 Stock	重量 Weight	標準価格 (Yen)
15760	1/8 - 28	JIS2	2.5P	120	16.5	10.5	8	5	D	51	8,500
15761				150						63	11,400
15765	1/4 - 19	JIS2	2.5P	120	19.5	12.5	11	5	D	89	9,900
15766				150						115	12,300
15770	3/8 - 19	JIS2	2.5P	120	21	14	14	5	D	144	15,800

■突き出しセンチ長さ・シャンク四角部寸法 ℓk , K はP.890をご覧ください。

1. タップ精度はめねじ精度を保証するものではありません。
2. 切削油剤、ペーストはP.868をご参照下さい。

ツールNo. EDP NO.	呼び Thread Size	精度 TAP Limit	食付 ℓc	全長 L	ねじ長 ℓ	軽径 ℓg	シャンク径 Ds	溝数 Flutes	在庫 Stock	重量 Weight	標準価格 (Yen)
15771	3/8 - 19	JIS2	2.5P	150	21	14	14	5	D	183	19,700
15775	1/2 - 14			150	27	17	18			285	23,000
15783	3/4 - 14			150	29	19	23			468	36,700
15791	1 - 11			150	35	22	26			617	55,200

■ Please see page 890 for length of external centre and shank square length ℓk and width K .

1. TAP Limit does not guarantee thread limit for the internal thread after tapping.
2. Cutting fluid and Paste : Please refer to P.868.

低炭素鋼 Low Carbon Steel	中炭素鋼 Medium Carbon Steel	高炭素鋼 High Carbon Steel	合金鋼 Alloy Steel	調質鋼 Hardened Steel	ステンレス鋼 Stainless Steel	工具鋼 Tool Steel	鋳鋼 Cast Steel	鋳鉄 Cast Iron	ダクタイル鋳鉄 Ductile Cast Iron	銅 Copper	黄銅 Brass	黄銅鑄物 Brass Casting	青銅 Bronze	アルミ圧延材 Aluminum Rolled	アルミ合金鑄物 Aluminum Alloy Casting	マグネシウム合金鑄物 Magnesium Alloy Casting	亜鉛合金鑄物 Zinc Alloy Casting	チタン合金 Titanium Alloy	Ni基合金 Nickel Alloy	熱硬化性プラスチック Thermo Setting Plastic	熱可塑性プラスチック Thermo Plastic
C ~0.25%	C0.25% ~0.45%	C 0.45%~	SCM	25~45 HRC 45~55 HRC 50~60 HRC	SUS	SKD	SC	FC	FCD	Cu	Bs	BsC	PB	AL	AC,ADC	MC	ZDC				
EX-LT-IRT																					
○					◎				○												
EX-LT-S-IRT																					
○					◎				○												

A、B、C、D=標準在庫品 A、B、C、D=Standard stock item.
□=特定代理店在庫品 □=Stocked by specific distributors. Contact us for price & availability.