

Metallic Slim

For cable exits in narrow spaces

■ Applications: For cable exits of small motors, sensors, measuring instruments and other wiring needs in a limited space

Model	Applicable cable diameter (mm)	Entry hole diameter (mm)	Threads	Working temperature	Weight	Q'ty per package	Lock nut model
OA-WS04M-20/25	φ 2-2.5	φ 4	M4 x 0.5	-25 to +100°C	2g	10 pcs.	LN-WS04M
OA-WS06M-25/40	φ 2.5-4	φ 6	M6 x 0.5		4g		LN-WS06M
OA-WS07M-35/50	φ 3.5-5	φ 7	M7 x 0.5		4g		LN-WS07M
OA-WS08M-45/60	φ 4.5-6	φ 8	M8 x 0.5		5g		LN-WS08M
OA-WS09M-55/70	φ 5.5-7	φ 9	M9 x 0.5		5g		LN-WS09M
OA-WS10M-65/80	φ 6.5-8	φ 10	M10 x 0.5		6g		LN-WS10M
OA-WS11M-45/60	φ 7.5-9	φ 11	M11 x 0.5		6g		LN-WS11MBS
OA-WS12M-55/70	φ 8.5-10	φ 12	M12 x 0.5		7g		LN-WS12MBS
OA-WS13M-65/80	φ 9.5-11	φ 13	M13 x 0.5		7g		LN-WS13MBS
OA-WS14M-65/80	φ 10.5-12	φ 14	M14 x 0.5		8g		LN-WS14MBS

*Above models are oilproof type. For the weatherproof type, see the "identification of model".



■ Identification of model

OA-WS□M-□/□□
 Nil ... Oilproof
 E ... Weatherproof
 Applicable cable ... φ 2~2.5
 diameter 20/25
 Thread size 04M ... M4

Multipurpose cable gland

OA-1 SERIES

Popular item since 1962. Flexible to different wire sizes.



Standard

Flexibly configurable to fit broad range of cable size.

■ Applications: For cable exits of various equipment including control panels, relay boxes, limit switches and motors.

Model	Applicable cable diameter (mm)				Entry hole dia. (mm)	Threads	Max. plate thickness	Working temp.	Weight	Q'ty per package
	1st. tier	2nd. tier	3rd. tier	4th. tier						
OA-05	φ 3.5-4.5	φ 4-6	φ 6-8	-	φ 17	G3/8 (PF3/8)	3mm	-25 to +70°C	11g	50 pcs.
OA-1	φ 4-5.5	φ 5.5-8	φ 8-10	φ 10-12	φ 21	CTG16 (G ¹ / ₂)	4mm		14g	20 pcs.
OA-15	φ 6-7	φ 7-11	φ 11-14	φ 14-16	φ 28	CTG22 (G ³ / ₄)	6mm		27g	10 pcs.
OA-2	φ 9-11	φ 11-14	φ 14-17	φ 17-19	φ 33.5	CTG28 (G1)	7.5mm		38g	5 pcs.
OA-S1 (※1)	φ 6-8	φ 8-10	φ 10-12	-	φ 21	CTG16 (G ¹ / ₂)	4mm		14g	20 pcs.

*1 Low-cost type

RoHS2

Color
Black



For thin steel Conduit

RoHS2

Color
Gray

For cable exits of CTC19 threaded thin steel conduits and electrical boxes

■ Applications: Provides secure clamping to cable exits from thin steel conduit by using with a coupling. For cable exits of outlet boxes, switch boxes, etc.

Model	Applicable cable diameter (mm)				Threads	Weight	Q'ty per package
	1st. tier	2nd. tier	3rd. tier	4th. tier			
OA-1 USU	φ 4-5.5	φ 5.5-8	φ 8-10	φ 10-12	CTC19	12g	20 pcs.

• Working temperature: -25 to +70°C

• Locknut is not attached. Use a CTC threaded nut for thin steel conduit if necessary.



For small valves

RoHS2

Color
Black

Well suited to DIN standard small valves

■ Applications: Electromagnetic valves connections in DIN standard terminal boxes

Model	Applicable cable diameter (mm)			Threads	Weight	Q'ty per package
	1st. tier	2nd. tier	3rd. tier			
OA-SD	φ 4-5	φ 6-8	φ 8-10	Pg11	10g	50 pcs.

• Working temperature: -25 to +70°C

• Locknut is not attached.



Distributor



OHM ELECTRIC CO., LTD.

7000-21, Nakagawa, Hosoe, Kita-ku, Hamamatsu, Shizuoka 431-1304, Japan

TEL +81-53-522-5562 FAX +81-53-523-2362 e-mail : info@ohm.co.jp

URL : <https://www.ohm.jp/>

The contents of this catalog are subject to change for product improvement.
Colors of products may slightly differ from actual due to printing.