



CoroMill® Plura solid carbide square shoulder end mill

Straight corner radius, center cut. Hardness $43 \leq \text{HRc} \leq 63$

End mills for roughing to semi-finishing in hardened steel

	R216.22..AI..G
CNSC	0
FHA	30°
BSG	COROMANT
TCDC	h9
TCDCON	h6



Metric version

DC	CZC _{MS}	APMX	RE	LU	ZEFP	Ordering code	P H		Dimensions		
							1610	1610	DCON	LF	DN
2.0	6	2.0	0.20	2.0	2	R216.22-02030AAI20G	☆	☆	6.0	57.0	
3.0	6	3.0	0.50	3.0	2	R216.22-03030BAI03G	☆	☆	6.0	57.0	
4.0	6	4.0	0.50	4.0	2	R216.22-04030BAI04G	☆	☆	6.0	57.0	
5.0	6	5.0	0.50	20.0	2	R216.22-05030BAI05G	☆	☆	6.0	57.0	4.9
6.0	6	6.0	1.00	21.0	2	R216.22-06030CAI06G	☆	☆	6.0	63.0	5.7
8.0	8	8.0	1.00	27.0	2	R216.22-08030CAI08G	☆	☆	8.0	72.0	7.7
10.0	10	10.0	1.50	32.0	2	R216.22-10030DAI10G	☆	☆	10.0	83.0	9.7
12.0	12	12.0	1.50	36.0	2	R216.22-12030DAI12G	☆	☆	12.0	83.0	11.8



E3



A231



A244



G2



G30



G20