


G-LIST No FL1063

高送りラジアスカッタ ねじ込みタイプ

High Feed Radius Cutter Screw Fit Type

PHC ねじ込みタイプ



■形状寸法表 Specification Chart

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	外径 Dc	カッタ 外径 D1	刃数 z	取付け径 Da	ねじサイズ Dg	スリサイズ Spanner Size	全長 l2	端面径 D	適用インサート Applicable Inserts	在庫 Stock	標準価格 (Yen)
7801500	PHC09R025SF12-3	13.2	25	3	12.5	12	17	35	23	SDMT09T3...	C	62,300
7801501	PHC09R028SF12-3	16.2	28	3	12.5	12	17	35	23		C	62,300
7801502	PHC09R030SF16-3	18.2	30	3	17	16	22	40	28		C	68,400
7801503	PHC09R032SF16-3	20.2	32	3	17	16	22	40	28		C	68,400
7801504	PHC09R035SF16-3	23.2	35	3	17	16	22	40	28		C	68,400
7801505	PHC09R040SF16-4	28.2	40	4	17	16	22	40	28	SXMT1204...	C	84,000
7801506	PHC12R030SF16-2	13.4	30	2	17	16	22	40	28		C	62,300
7801507	PHC12R032SF16-2	15.4	32	2	17	16	22	40	28		C	62,300
7801508	PHC12R035SF16-3	18.4	35	3	17	16	22	40	28		C	75,400
7801509	PHC12R040SF16-3	23.4	40	3	17	16	22	40	28		C	77,000

※シャンクホルダはP640~642をご参照ください。


※Please see P640~642 for shank holders.

G-LIST No FL1067

仕上げ用ボールエンドミル ねじ込みタイプ

Finishing Ball End Mill Screw Fit Type

PFB ねじ込みタイプ



■形状寸法表 Specification Chart

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	外径 Dc	刃数 z	取付け径 Da	ねじサイズ Dg	スリサイズ Spanner Size	全長 l2	首径 d2	端面径 D	適用インサート Applicable Inserts	在庫 Stock	標準価格 (Yen)
7801490	PFB-R100SF6	10	2	6.5	6	7	26	9	9	PFB...	C	15,500
7801491	PFB-R120SF6	12	2	6.5	6	7	26	11	11		C	16,100
7801492	PFB-R160SF8	16	2	8.5	8	10	32	14	14.5		C	18,700
7801493	PFB-R200SF10	20	2	10.5	10	14	38	18	18		C	20,800
7801494	PFB-R250SF12	25	2	12.5	12	17	38	22	23		C	24,700
7801495	PFB-R300SF16	30	2	17	16	22	43	27	28		C	32,100

※シャンクホルダはP640~642をご参照ください。


※Please see P640~642 for shank holders.

G-LIST No FL1080

仕上げ用ラジアスエンドミル ねじ込みタイプ

Finishing Radius End Mill

PFR ねじ込みタイプ



■形状寸法表 Specification Chart

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	外径 Dc	刃数 z	取付け径 Da	ねじサイズ Dg	スリサイズ Spanner Size	全長 l2	首径 d2	端面径 D	適用インサート Applicable Inserts	在庫 Stock	標準価格 (Yen)
7832090	PFR-R100SF6	10	2	6.5	6	7	26	9	9	PFR...	C	15,500
7832091	PFR-R120SF6	12	2	6.5	6	7	26	11	11		C	16,100
7832092	PFR-R160SF8	16	2	8.5	8	10	32	15	14.5		C	18,700
7832093	PFR-R200SF10	20	2	10.5	10	14	38	19	18		C	20,800
7832094	PFR-R250SF12	25	2	12.5	12	17	38	24	23		C	24,700
7832095	PFR-R300SF16	30	2	17	16	22	43	29	28		C	32,100
7832096	PFR-R320SF16	32	2	17	16	22	43	31	28		C	35,800

※シャンクホルダはP640~642をご参照ください。

※Please see P640~642 for shank holders.