


CoroTurn® 107 shank tool for turning


Screw clamp design




RCMT
RCGX-AL







SRDCN



SRDCR/L



Metric version

							Ordering code	Dimensions						 		MIID
		CZC _{MS}	LU	OHX	CNSC	B		H	LF	WF	HF	Nm	Kg			
	05	10 x 10	10	14	0	SRDCN 1010E 05	10	10	70	7	10	0.9	0.08	RCMT 05 02 M0		
	06	12 x 12	12	12	0	SRDCN 1212F 06	12	12	80	9	12	0.9	0.09	RCMT 06 02 M0		
	08	16 x 16	16	16	0	SRDCN 1616H 08	16	16	100	12	16	1.4	0.62	RCMT 08 03 M0		
	10	20 x 20	25	25	0	SRDCN 2020K 10-A	20	20	125	15	20	3.0	0.40	RCMT 10 T3 M0		
		25 x 25	25	25	0	SRDCN 2525M 10-A	25	25	150	17	25	3.0	0.66	RCMT 10 T3 M0		
		32 x 25	28	28	0	SRDCN 3225P 10-A	25	32	170	17	32	3.0	1.00	RCMT 10 T3 M0		
	12	20 x 20	25	25	0	SRDCN 2020K 12-A	20	20	125	16	20	3.0	0.40	RCMT 12 04 M0		
		25 x 25	28	28	0	SRDCN 2525M 12-A	25	25	150	18	25	3.0	0.66	RCMT 12 04 M0		
		32 x 25	28	28	0	SRDCN 3225P 12-A	25	32	170	18	32	3.0	1.00	RCMT 12 04 M0		
	16	25 x 25	35	35	0	SRDCN 2525M 16-A	25	25	150	20	32	6.4	1.00	RCMT 16 06 M0		
		32 x 25	35	35	0	SRDCN 3225P 16-A	25	32	170	20	32	6.4	1.00	RCMT 16 06 M0		
	20	32 x 32	40	40	0	SRDCN 3232P 20-A	32	32	170	26	32	9.5	1.20	RCMT 20 06 M0		
	05	32 x 25	20	35	0	SRDCR/L 3225P 05-A	25	32	170	25	32	0.9	1.00	RCMT 05 02 M0		
	06	20 x 20	20	32	0	SRDCR/L 2020K 06-A	20	20	125	20	20	0.9	0.40	RCMT 06 02 M0		
		32 x 25	20	35	0	SRDCR/L 3225P 06-A	25	32	170	25	32	0.9	1.00	RCMT 06 02 M0		
	08	20 x 20	20	32	0	SRDCR/L 2020K 08-A	20	20	125	20	20	1.4	0.40	RCMT 08 03 M0		
		25 x 25	20	35	0	SRDCR/L 2525M 08-A	25	25	150	25	25	1.4	0.68	RCMT 08 03 M0		
		32 x 25	20	35	0	SRDCR/L 3225P 08-A	25	32	170	25	32	1.4	1.00	RCMT 08 03 M0		

N = Neutral, R = Right hand, L = Left hand



A7



I1



F16



I38



I21