


PB 300







Dead-blow mallet with plastic head

- for straightening workpieces on machine tables
- for recoilless blows during assembly work
- inserts made of particularly tough, wear-resistant plastic, for an exceptionally long service life
- handle made of FSC® certified hickory wood, non-slip, robust and durable
- handle securely fastened in tube with special wedge and heavy dowel pin, but easily replaceable
- recoil damping due to weights in the hammer head, for firm, accurate blows without recoil
- pay attention to the safety regulations when working with striking tools: www.pbst.ch/safe

Martillo de goma, sin rebote

- para rectificar piezas en mesas de máquinas
- para golpes delicados en trabajos de montaje
- insertos de plástico especialmente resistente y duro para una vida útil extraordinariamente larga
- mango de madera Hickory con certificación FSC®, de fácil agarre, resistente y duradero
- fijación segura en el tubo del mango con cuña especial y pasador elástico pesado, sustitución sencilla
- amortiguación de rebotes mediante pesos en cabeza de martillo, para golpes intensos y precisos sin rebote
- observe siempre las normas de seguridad cuando trabaje con herramientas de percusión: www.pbst.ch/safe



	∅						
PB 300.1	22	270	1	75	167	10	7 610733 003648
PB 300.2	27	290	2	90	274	10	7 610733 003655
PB 300.3	32	320	3	100	391	10	7 610733 003662
PB 300.4	35	330	4	105	466	10	7 610733 003679
PB 300.5	40	355	5	110	695	10	7 610733 003686
PB 300.6	50	385	6	110	1050	6	7 610733 003693
PB 300.7	60	420	7	120	1470	6	7 610733 003709