


CoroMill® 390 insert for milling

KRINS 90°



	RE	BS	Ordering code	P		M		K		N		S		H		Dimensions, mm, inch							
				1020	1025	1030	2040	4220	4230	4240	530	1025	1030	1040	2030	2040	4240	530	1020	1025	1030	3040	4220
	18	1.2	0.3	R390-18 06 12M-MMR														11.0	15.4	6.33			
		.047	.010																.433	.606	.249		
	11	0.2	0.7	R390-11 T3 02E-KM						*			*			*		6.8	10.0	3.59			
		.008	.028																.268	.394	.141		
		1.2	0.8	R390-11 T3 12E-KM							*		*			*			6.8	10.0	3.59		
		.047	.031																.268	.394	.141		
		1.6	0.8	R390-11 T3 16E-KM							*		*			*			6.8	10.0	3.59		
		.063	.031																.268	.394	.141		
		2.0	0.4	R390-11 T3 20E-KM							*		*			*			6.8	10.0	3.59		
		.079	.016																.268	.394	.141		
		2.4		R390-11 T3 24E-KM							*		*			*			6.8	10.0	3.59		
		.094																	.268	.394	.141		
		3.1		R390-11 T3 31E-KM							*		*			*			6.8	10.0	3.59		
		.122																	.268	.394	.141		
		17	0.4	1.0	R390-17 04 04E-KM						*		*			*			9.6	15.7	4.76		
		.016	.039																.378	.618	.187		
		1.2	1.1	R390-17 04 12E-KM							*		*			*			9.6	15.7	4.76		
		.047	.043																.378	.618	.187		
		1.6	0.7	R390-17 04 16E-KM							*		*			*			9.6	15.7	4.76		
	.063	.028																.378	.618	.187			
	2.0	0.3	R390-17 04 20E-KM							*		*			*			9.6	15.7	4.76			
	.079	.012																.378	.618	.187			
	2.4		R390-17 04 24E-KM							*		*			*			9.6	15.7	4.76			
	.094																	.378	.618	.187			
	3.1		R390-17 04 31E-KM							*		*			*			9.6	15.7	4.76			
	.122																	.378	.618	.187			
	4.0		R390-17 04 40E-KM							*		*			*			9.6	15.7	4.76			
	.157																	.378	.618	.187			
	4.8		R390-17 04 48E-KM							*		*			*			9.6	15.7	4.76			
	.189																	.378	.618	.187			
	5.0		R390-17 04 50E-KM							*		*			*			9.6	15.7	4.76			
	.197																	.378	.618	.187			
	6.0		R390-17 04 60E-KM							*		*			*			9.6	15.7	4.76			
	.236																	.378	.618	.187			
	6.4		R390-17 04 64E-KM							*		*			*			9.6	15.7	4.76			
	.250																	.378	.618	.187			
	11	0.4	0.9	R390-11 T3 04M-KM						*	*	*	*		*		*	6.8	10.0	3.59			
		.016	.035																.268	.394	.141		
		0.8	1.2	R390-11 T3 08M-KM							*	*	*	*		*		*	6.8	10.0	3.59		
		.031	.047																.268	.394	.141		
		1.6	0.4	R390-11 T3 16M-KM							*	*	*	*		*		*	6.8	10.0	3.59		
	.063	.016																.268	.394	.141			
	3.1		R390-11 T3 31M-KM							*	*	*	*		*		*	6.8	10.0	3.59			
	.122																	.268	.394	.141			




J474



J508



Q1



Q17

