

KF Series

Dimensions

Straight Union: KFH




Resin sleeve



Brass sleeve

Applicable tubing size (mm)		Model	Width across flats		L ₁	L ₂	M	ød	Effective area (mm ²)	Weight (g)
O.D.	I.D.		H ₁	H ₂						
ø4	ø2.5	KFH04-00	8	10	40.9	27.6	15.5	1.5	1.6	13
		KFH04B-00			34.7	28.8	12.4			14
ø6	ø4	KFH06-00	10	12	40.3	27	15.2	3	6	17
		KFH06B-00			34.3	28.4	12.2			19
ø8	ø5	KFH08U-00	12	14	41.3	28	16.2	4	11	23
		KFH08N-00			35.5	29.6	13			22
ø8	ø6	KFH08B-00	12	14	35.5	29.6	13	5	17	24
		KFH08N-00			44.6	30	18.8			36
ø10	ø6.5	KFH10U-00	17	17	44.6	30	18.8	5.5	21	36
		KFH10N-00			37.0	31.0	15.0			39
ø10	ø7.5	KFH10B-00	17	17	37.0	31.0	15.0	6.5	30	42
		KFH10N-00			45.5	32	19.3			41
ø12	ø8	KFH12U-00	17	19	45.5	32	19.3	7	35	44
		KFH12N-00			38.1	32.2	15.5			41
ø12	ø9	KFH12B-00	17	19	38.1	32.2	15.5	8	45	44
		KFH12N-00			38.1	32.2	15.5			44



Tee Union: KFT



Resin sleeve



Brass sleeve

Applicable tubing size (mm)		Model	Width across flats		L ₁	L ₂	M	ød	Effective area (mm ²)	Weight (g)
O.D.	I.D.		H ₁	H ₂						
ø4	ø2.5	KFT04-00	10	10	27.5	20.8	15.5	1.5	1.6	33
		KFT04B-00			24.4	21.4	12.4			35
ø6	ø4	KFT06-00	10	12	27.2	20.5	15.2	3	6	37
		KFT06B-00			24.2	21.2	12.2			39
ø8	ø5	KFT08U-00	12	14	30.2	23.5	16.2	4	11	54
		KFT08N-00			27.3	24.3	13.3			56
ø8	ø6	KFT08B-00	12	14	27.3	24.3	13.3	5	17	53
		KFT08N-00			31.8	24.5	18.8			65
ø10	ø6.5	KFT10U-00	12	17	31.8	24.5	18.8	5.5	21	65
		KFT10N-00			28.0	25.0	15.0			67
ø10	ø7.5	KFT10B-00	12	17	28.0	25.0	15.0	6.5	30	63
		KFT10N-00			34.3	27.5	19.3			89
ø12	ø8	KFT12U-00	14	19	34.3	27.5	19.3	7	35	89
		KFT12N-00			30.6	27.6	15.5			85
ø12	ø9	KFT12B-00	14	19	30.6	27.6	15.5	8	45	90
		KFT12N-00			30.6	27.6	15.5			90

