



AMC Series

Construction/Dimensions

Male thread



Female thread



Drain piping type

Model	Port size	(mm)														
		A	B			C	Mounting bracket								Drain piping	
			R	NPT	G		E	F	G	H	J	K	Rc	NPT	G	B'
AMC310	$\frac{3}{8}$	151	139	134	141	75	M3 x 0.5 Depth 8	24	50	15	55	2.3	142	137		
AMC510	$\frac{3}{4}$	204	197	189	194	102	M4 x 0.7 Depth 10	40	70	20	70	3.2	200	192		
AMC610	1	230	225	217	220	118	M4 x 0.7 Depth 10	48	70	20	80	3.2	228	220		
AMC810	$1\frac{1}{2}$	-	270		-	135	-	-	-	-	-	-	-	273		
AMC910	2	-	327		-	153	-	-	-	-	-	-	-	330		

Drain piping type

Model	Port size	A	B	C	(mm)										
					D	Mounting bracket								Drain piping	
						E	F	G	H	J	K	L	Rc	NPT	G
AMC220	$\frac{1}{4}$	100	88	56	M3 x 0.5 Depth 8	22	40	2.3	15	12	20	50	91		
AMC320	$\frac{1}{4}, \frac{3}{8}$	141	121	75	M3 x 0.5 Depth 8	24	55	2.3	15	20	30	50	124		
AMC520	$\frac{1}{2}, \frac{3}{4}$	194	174	102	M4 x 0.7 Depth 10	40	70	3.2	20	20	30	70	177		

How to Order Oil Bowl Assembly

If the oil case becomes damaged, it can be replaced easily.

AMC - CA 3 - A

Size


Thread type Applicable to drain piping

Symbol	Applicable model
2	AMC220
3	AMC310, 320
5	AMC510, 520
6	AMC610
8	AMC810
9	AMC910

Exhaust of oil mist	
Symbol	Type
A	Drain cock (Standard)
D	Drain piping

Symbol	Type
Nil	Rc
N	NPT
F	G

Note) Select the threads to match the threads on the product itself.



Drain cock

Drain piping type

* Without a valve function

	(mm)		
Body size	A	B	C
2	56	59	56
3	66	69	75
5	83	86	102
6	96	99	118
8	96	99	135
9	116	119	153