



TOGGLE CLAMP (Vertical Handle Type)

TD34S



Item No.	Base type	N.W.(g)
TD34S	Straight	2320

- Max. holding capacity : 5.0kN
- Clamp arm moving angle : 128°
- Handle operation angle : 68°
- Supporting pin : stainless steel

TOGGLE CLAMP (Push Type)

TP02F



Item No.	Base type	N.W.(g)
TP02F	Flange	368

- Max. holding capacity : 1.8kN
- Stroke : 30mm
- Handle operation angle : 145°
- Supporting pin : stainless steel

TP06F



Item No.	Base type	N.W.(g)
TP06F	Flange	60

- Max. holding capacity : 0.5kN
- Stroke : 13mm
- Handle operation angle : 93°
- Supporting pin : stainless steel

TP07F



Item No.	Base type	N.W.(g)
TP07F	Flange	100

- Max. holding capacity : 0.5kN
- Stroke : 10mm
- Handle operation angle : 66°
- Supporting pin : stainless steel

