




Installation Example



Installation Example



Components

Plate material	Plate finish	Spring material	Spring finish
Brass	Nickel plated	Stainless steel SUS304	Unfinished
		Steel wire	Nickel plated


Product no. / Feature

Product no.	Spring diameter	Spring material	Matching battery / Details	Weight (g)	Pack of
IT-1SP	—	—	D : + (Positive)	1.2	10
IT-1SM	Φ1.0	Stainless steel SUS304	D : - (Negative)	2.5	10
IT-1WP	Φ1.0	Stainless steel SUS304	D : Left + (Positive) • Right - (Negative)	5.0	10
IT-1WM	Φ1.0	Stainless steel SUS304	D : Left - (Negative) • Right - (Positive)	5.0	10
IT-2SP	—	—	C : + (Positive)	0.9	10
IT-2SM	Φ0.7	Steel wire	C : - (Negative)	1.4	10
IT-2WP	Φ0.7	Steel wire	C : Left + (Positive) • Right - (Negative)	2.7	10
IT-2WM	Φ0.7	Steel wire	C : Left - (Negative) • Right - (Positive)	2.7	10
IT-3SP	—	—	AA : + (Positive)	0.4	10
IT-3SM	Φ0.6	Steel wire	AA : - (Negative)	0.7	10
IT-3WP	Φ0.6	Steel wire	AA : Left + (Positive) • Right - (Negative)	1.1	10
IT-3WM	Φ0.6	Steel wire	AA : Left - (Negative) • Right - (Positive)	1.1	10
IT-4SP	—	—	AAA : + (Positive)	0.2	10
IT-4SM	Φ0.5	Steel wire	AAA : - (Negative)	0.4	10
IT-4WP	Φ0.5	Steel wire	AAA : Left + (Positive) • Right - (Negative)	0.6	10
IT-4WM	Φ0.5	Steel wire	AAA : Left - (Negative) • Right - (Positive)	0.6	10


IT dimensions

■ DXF/DWG/PDF drawings available on our website.


IT-1SP



IT-1WP



IT-1SM



IT-1WM

