

The number next to the logo mark indicates items in stock for each brand.




Stock 38,650 Items

Soft Jaw (for NIKKO)



- Features
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin
- Japan



N Type (3 pieces 1 set)

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-9228	N-5	¥ 4,842	¥ 5,230	5	1.5	60	26.0	34	1	0.95
112-9236	N-6	¥ 5,498	¥ 5,940	6	1.5	80	27.5	35	1	1.40
112-9325	N-8	¥ 6,138	¥ 6,630	8	1.5	103	34.0	40	1	2.70
112-9333	N-10	¥10,516	¥11,360	10	1.5	110	44.0	50	1	4.80
112-9341	N-12	¥11,340	¥12,250	12	1.5	120	44.0	50	1	5.20
112-9350	N-14	¥26,651	¥28,790	14 to 16	1.5	150	49.0	75	1	13.90
112-9481	HNK-6-45	¥ 7,591	¥ 8,200	6	1.5	80	27.5	45	1	1.80
112-9490	HNK-6-60	¥ 7,739	¥ 8,360	6	1.5	80	27.5	60	1	2.50
112-9503	HNK-8-60	¥ 9,683	¥10,460	8	1.5	103	34.0	60	1	4.10
112-9511	HNK-8-90	¥14,839	¥16,030	8	1.5	103	34.0	90	1	6.20
112-9520	HNK-10-60	¥14,126	¥15,260	10	1.5	110	44.0	60	1	5.70
112-9538	HNK-10-90	¥23,050	¥24,900	10	1.5	110	44.0	90	1	8.50

Contact us:0120-509-849 <http://www.orange-book.com/>




Stock 38,650 Items

Soft Jaw (for Victor)



- Features
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin
- Japan



SJ Type (3 pieces 1 set)

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-8621	SJ-70	¥ 8,424	¥ 9,100	6	-	70	30	36	1	1.50
112-8639	SJ-85	¥10,127	¥10,940	7-8	-	85	30	38	1	1.93
112-8647	SJ-100	¥12,849	¥13,880	9-10	-	100	35	46	1	3.30
112-8655	SJ-115	¥16,718	¥18,060	12	-	115	40	49	1	4.48
112-8663	SJ-135	¥29,373	¥31,730	15	-	135	43	53	1	6.20
112-8671	SJ-135H	¥34,548	¥37,320	18	-	135	50	67	1	9.00

Contact us:0120-509-849 <http://www.orange-book.com/>




Stock 38,650 Items

Soft Jaw (for MATSUMOTO)



- Features
- S45C steel which is easy to modify and has suitable hardness is used.
 - Careful processing has been given considering points such as lowering of restoration accuracy (Core run out) after reinstallation and factors causing attachment distortion of the Master Jaw.
- Origin
- Japan



M Type (3 pieces 1 set)

Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Chuck Outer Diameter (inch)	Pitch (mm)	Length (mm)	Width (mm)	Height (mm)	SPQ (set)	Weight (kg/set)
112-9139	M-6	¥ 5,230	¥ 5,650	6	1.5	80	27.5	34	1	1.40
112-9147	M-8X	¥ 6,332	¥ 6,840	8	1.5	90	36.0	40	1	2.40
112-9155	M-10	¥ 9,683	¥10,460	10	1.5	103	40.0	48	1	3.90
112-9163	M-12	¥12,237	¥13,220	12	1.5	140	50.0	50	1	7.00
112-9171	M-15	¥25,661	¥27,720	15 to 22	3.0	150	62.0	62	1	10.80

Contact us:0120-509-849 <http://www.orange-book.com/>