








Type	Swing Check			Strainer			Strainer			Ball			Ball			
<b>U-Series</b>																
Fig	<b>UNSF-N</b>			<b>UT-N</b>			<b>UTF-N</b>			<b>UZ-N</b>			<b>UZ-N-T</b>			
Product Code	<b>804J</b>			<b>809</b>			<b>809J</b>			<b>3550</b>			<b>3550W</b>			
inch	mm	L	H	D1	L	H	H1*	L	H	H1*	L	H	D	L	H	D
1/4	8										39	31	60	39	25	35
3/8	10										44	36	70	44	29	40
1/2	15	85	45		85	58	79	120	58	79	56.5	41	85	56.5	35	55
3/4	20	95	55		100	64	89	130	66	91	59	44	85	59	39	55
1	25	110	61		115	76	107	150	78	109	71	48	100			
1	32	130	71		135	89	127	170	93	131	78	54	100			
1 1/2	40	150	72		150	98	139	190	104	144	83	65	125			
2	50	180	81		180	115	167	220	121	173	100	72	125			
Body	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Bonnet/Cap/Cover				Stainless Steel			Stainless Steel									
Stem	Stainless Steel									Stainless Steel			Stainless Steel			
Disc/Ball	Stainless Steel									Stainless Steel			Stainless Steel			
Hinge Pin	Stainless Steel															
Plug	Stainless Steel															
Screen				Stainless Steel			Stainless Steel									
Seat										R-PTFE			R-PTFE			
Note				*Height for removing the screen			*Height for removing the screen			Standard Bore			Standard Bore T-Handle			

Type	Ball			Wafer Check			
							
Fig	<b>A10-UBF-L</b>			<b>10-UNW</b>			
Product Code	<b>3011L</b>						
inch	mm	L	H	D	L	H	D
1/2	15	108	102	130			
3/4	20	117	105	130			
1	25	127	124	160			
1 1/4	32	140	128	160			
1 1/2	40	165	115	230	54	118	63
2	50	178	120	230	60	126	63
2 1/2	65	190	155	400	67	134	63
3	80	203	165	400	73	138	63
4	100	229	200	460	73	151	63
5	125	356	220	460	86	174	70
6	150	394	295	1000	98	188	70
8	200	457	355	1500	127	215	70
10	250				146	254	80
12	300				181	282	80
Body	Stainless Steel			Stainless Steel			
Bonnet/Cap/Cover	Stainless Steel						
Stem	Stainless Steel						
Disc/Ball	Stainless Steel			Stainless Steel			
Seat Rubber				NBR			
Note	Full Bore						