

LOW PROFILE SOCKET HEAD CAP SCREW

(F02 SERIES)


GLOBAL STANDARD COMPONENTS

TM **NAAMS**



Assembly

07/25/08



DIMENSIONS								
NOM. THREAD SIZE	PITCH	A MAX	B MAX	C MIN	D MIN	H MAX	T MIN	W NOM
M4	0.7	7.0	4	1.06	1.48	2.8	20	3
M5	0.8	8.5	5	1.39	1.85	3.5	22	4
M6	1.0	10.0	6	1.65	2.09	4.0	24	5
M8	1.25	13.0	8	2.24	2.48	5.0	28	6
M10	1.5	16.0	10	2.86	3.36	6.5	32	8
M12	1.75	18.0	12	3.46	4.26	8.0	36	10
M16	2.0	24.0	16	4.91	4.76	10.0	44	12
M20	2.5	30.0	20	6.10	6.07	12.5	52	14

THREAD SIZE NOM.	STOCK SIZES (L)																
	8	10	12	16	20	25	30	35	40	45	50	55	60	70	80	90	100
M4																	
M5																	
M6																	
M8																	
M10																	
M12																	
M16																	
M20																	

- Lengths to the left of heavy line (■) threaded to head.
- Lengths to the right of heavy line (■) have standard minimum thread lengths of two times the nominal thread diameter plus 12 mm.

NOTES & SPECIFICATIONS:

Material, class 10.9

CODING ON FOLLOWING PAGE

B

C

A

D