






Joint Clips (Type-R) (Type-S) Same Diameter Type




Type-R



Type-S



Applicable Shafts



Thrust Loading

Type-R (Product Code: 171)

Unit: mm

Dimensions Code	Nominals No.	Dimensions																Applicable Shafts			Thrust Load N	
		t		H ₁		H ₂	H ₃	H ₄		L ₁	L ₂		L ₃	L ₄	B		W					
		Basic Dimension	Tolerance	Basic Dimension	Tolerance			Basic Dimension	Tolerance		Basic Dimension	Tolerance			Basic Dimension	Tolerance	Basic Dimension	Tolerance	Basic Dimension	Tolerance		G
71040	4	0.5	±0.012	5.0	—	4.0	9.0	—	—	—	—	—	11.0	—	5.5	±0.1	11.5	±0.1	11.0	13.0	5.5	2,128.0

Type-S (Product Code: 170)

Unit: mm

Dimensions Codes	Nominals No.	Dimensions																Applicable Shafts			Thrust Load N		
		t		H ₁		H ₂	H ₃	H ₄		L ₁	L ₂		L ₃	L ₄	B		W		G	S		m	
		Basic Dimension	Tolerance	Basic Dimension	Tolerance			Basic Dimension	Tolerance		Basic Dimension	Tolerance			Basic Dimension	Tolerance	Basic Dimension	Tolerance					
70060	6	0.7	±0.03	8.2	+0.3 -1.0	5	18.3	8.0	+0.45 -0.15	4.6	+0.4	6.3	13.2	18.2	6.0	±0.1	12	±0.1	13.0	16.0	5.5	5,070.0	
70080	8			9.7		6	21.1	8.8		6.4		14.2	19.9	15.0					17.0	4,942.6			
70100	10			11.2		8	23.9	9.7		4.0		14.7	20.8	17.0					20.0	4,746.4			
70127	12.7	0.8	±0.04	14.5	+0.5 -1.5	8.8	30.0	12.75	+0.45 -0.15	5.1	+0.4	7.1	18.4	26.5	6.0	±0.1	14	±0.1	22.0	25.0	5.5	6,786.2	
70160	16A			16.4				34.5		14.1		4.1	6.1	19.5					28.6	26.0		30.0	6,864.7
71016	16B			18.4				38.5		16.0		5.7	8.5	23.5					33.7	28.0		34.0	7,649.2
70222	22.2	0.9	±0.04	21.7	+0.7 -1.8	10	44.5	17.0	+0.45 -0.15	7.9	+0.4	7.2	26.2	37.3	6.0	±0.1	16	±0.1	32.0	38.0	5.5	8,777.0	
70254	25.4			24.7				51.8		19.6		5.3	7.2	30.2					42.9	38.0		44.0	12,474.1

Remarks: The value of thrust load represents the average of measured values under our measurement methodology.

Notes: The nominal size No. 4 is applicable only for Type-R. The product code is 171.

Product code	170 (Type-S)		Material code	02...SUS304-CSP			Part Number Structure (Standardized Product Code)					
	171 (Type-R)						Product		Surface		Example: Nominal 12.7	
Surface code	01...Material Texture				Hardness		1 7 0 0 2 0 1 Material 7 0 1 2 7 Dimensions					