


A10636 Urethane AG type

Insulated hinged hanging band for suspended cold and hot water pipe



Part number A10636 Urethane AG type

Unit (mm)

Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	c	Hanging bolt diameter	Thermal insulation thickness (T) 20 mm		Thermal insulation thickness (T) 25 mm		Thermal insulation thickness (T) 30 mm		Thermal insulation thickness (T) 40 mm		Thermal insulation thickness (T) 50 mm	
						Size code	H	Size code	H	Size code	H	Size code	H	Size code	H
15A	1/2	21.7	2.3	25	W 3/8	0014	90	0029	96	0033	102				
20A	3/4	27.2	2.3	25	W 3/8	0048	95	0052	100	0067	103	0071	116		
25A	1	34.0	2.3	25	W 3/8	0086	98	0103	103	0118	108	0122	118		
32A	1 1/4	42.7	2.3	25	W 3/8	0137	102	0141	111	0156	116	0175	123		
40A	1 1/2	48.6	2.3	25	W 3/8	0180	106	0194	114	0207	119	0211	129		
50A	2	60.5	2.3	25	W 3/8	0226	110	0245	120	0250	125	0264	135		
65A	2 1/2	76.3	2.6	32	W 3/8	0279	118	0283	128	0298	133	0315	143		
80A	3	89.1	2.6	32	W 3/8	0320	123	0334	134	0349	139	0353	149	0368	159
100A	4	114.3	2.6	32	W 3/8			0372	146	0387	151	0391	161	0404	171
125A	5	139.8	4.5	32	W 1/2			0419	172	0423	177	0438	187	0442	197
150A	6	165.2	4.5	32	W 1/2			0457	184	0461	189	0476	199	0495	209
200A	8	216.3	6.0	38	W 3/8					0508	237	0512	247	0527	257


A10647 Urethane AG type with stainless steel band

Insulated hinged hanging band for suspended cold and hot water pipe

Part number A10647

Urethane AG type with stainless steel band

Unit (mm)



Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	c	Hanging bolt diameter	Thermal insulation thickness (T)				
						20 mm	25 mm	30 mm	40 mm	50 mm
15A	1/2	21.7	2.0	25	W 3/8	0018	0022	0037		
20A	3/4	27.2	2.0	25	W 3/8	0041	0056	0075	0080	
25A	1	34.0	2.0	25	W 3/8	0094	0107	0111	0126	
32A	1 1/4	42.7	2.0	25	W 3/8	0145	0150	0164	0179	
40A	1 1/2	48.6	2.0	25	W 3/8	0183	0198	0215	0220	
50A	2	60.5	2.0	25	W 3/8	0234	0249	0253	0268	0610
65A	2 1/2	76.3	2.0	32	W 3/8	0272	0287	0291	0304	0624
80A	3	89.1	2.0	32	W 3/8	0319	0323	0338	0342	0357
100A	4	114.3	2.0	32	W 3/8		0361	0376	0395	0408
125A	5	139.8	4.0	32	W 1/2		0412	0427	0431	0446
150A	6	165.2	4.0	32	W 1/2		0465	0470	0484	0499
200A	8	216.3	6.0	38	W 3/8		0501	0516	0516	0535