


Prices displayed include 8% tax.


Stock
38,650
 Items

Cup Brush for Electric Tool

GCB-75
(brass plating steel wire)GCB-75S
(stainless steel)GCB-90
(brass plating steel wire)GCB-125
(brass plating steel wire)

- Features**
- Burring, rust remover, demonstrate its power in paint removal.
 - Optimum for fine small burring after cutting and grinding.
- Use**
- For Flat Surface Polishing
 - Rust prevention and polishing of iron and steel/non-ferrous metals, burring of welding, paint removal, base polishing, edge finishing of rubber production process, surface processing.
- Specs**
- Compatible grinders: whetstone diameter 100mm (GCB-75, 75S) whetstone diameter 125, 150mm (GCB-90) whetstone diameter 180, 205mm (GCB-125) for electric tools
 - Metal fitting diameter: 71mm (GCB-75, 75S), 83mm (GCB-90), 110mm (GCB-125)
- Origin**
- Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
124-7620	GCB-75	¥1,351	¥1,460	75	0.27	Brass Plating Steel Wire	M10 (P1.5)	12000	10	305
124-7638	GCB-75S	¥2,851	¥3,080	75	0.30	Stainless Steel	M10 (P1.5)	12000	10	310
124-7646	GCB-90	¥2,370	¥2,560	85	0.27	Brass Plating Steel Wire	M16 (P2.0)	9500	10	520
124-7654	GCB-125	¥4,064	¥4,390	120	0.38	Brass Plating Steel Wire	M16 (P2.0)	8000	10	895

1 Box (30 pieces)

Warning
• Not individual packaging.

Order Unit: 1 Box

Estimated Unit Price per Piece
¥1,284

Order Code	Item No.	Price (per box)	MSRP (per box)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	Qty Per Box (piece)	SPQ (box)	Weight (kg/box)
471-4482	GCB-75-30P	¥38,510	¥41,600	75	0.27	Brass Plating Steel Wire	M10 (P1.5)	12000	30	1	9.15

Contact us: 0120-509-849 <http://www.orange-book.com/>
Stock
38,650
 Items

Cup Brush for Air Tool

GCB-75AC
(brass plating steel wire)GCB-75AS
(stainless steel)

- Features**
- Since brushes are not abrasives like grinding wheels and coated whetstone abrasive piece, they do not scrape the products themselves, they are optimum for removing dirt and deposits on the surface.
- Use**
- For Flat Surface Polishing
 - Rust remover/oxide film removal after welding.
 - Paint removal and ground processing.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Pneumatic Tools
- Origin**
- Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Hole Diameter (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
352-0676	GCB-75AC	¥1,389	¥1,500	75	0.27	Brass Plating Steel Wire	16	13600	10	270
352-0668	GCB-75AS	¥2,777	¥3,000	75	0.30	Stainless Steel	16	13600	10	270

Contact us: 0120-509-849 <http://www.orange-book.com/>
Stock
38,650
 Items

Cup Brush for Electric Tool (abrasive grain-filled nylon)



GCB-75GN

- Features**
- Compared to metal wire brushes, scattering of wire rods is less, and this is cup brushes emphasizing safety.
 - Compared to conventional nylon string wires with abrasive grains, bristles with less burning to the work due to wear heat are used.
 - Compared to metal wire brushes, usability is improved because weight reduction is attempted.
- Use**
- For flat surface polishing.
 - Paint removal, rust remover, polishing after welding.
- Specs**
- Compatible Grinder: Grinding Wheel Diameter 100mm for Electric Tools
- Origin**
- Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Bristle Material	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
480-5666	GCB-75GN	¥2,851	¥3,080	75	1.2	Abrasive Grain Nylon String # 80	M10 (P1.5)	12000	30	162

Contact us: 0120-509-849 <http://www.orange-book.com/>
Stock
54
 Items

"MP Grid Brush"



75EN-110N0

- Features**
- The grid wires have both safe chemical fiber wires and steel wires with powerful grinding performance and the grid placed across the entire surface of the wires prevents scratching of the work surface.
 - By improving heat resistance, the problem with welding due to heat from wear has also been resolved.
 - The grid wires reduce the danger of the cup brush and realize even safer work.
- Use**
- Rust and coating removal from piping and tanks, etc. of plant facilities.
- Specs**
- Bristle: N-GRIT wires
- Origin**
- Japan

Order Unit: 1 Piece

MITACHI TOOLS CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Grit count (#)	Wire Diameter (mm)	Screw Diameter	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
791-9191	75EN-110N3	¥1,620	¥1,900	95	46	1.9	M10 (P1.5)	5000 to 8000	50	156
791-9166	75EN-110N0	¥1,620	¥1,900	95	60	1.3	M10 (P1.5)	5000 to 8000	50	156
791-9174	75EN-110N1	¥1,620	¥1,900	95	120	1.2	M10 (P1.5)	5000 to 8000	50	156
791-9182	75EN-110N2	¥1,620	¥1,900	95	240	0.9	M10 (P1.5)	5000 to 8000	50	156

Contact us: 0120-598-307 <http://www.sanko-mitachi.com/>